

**Profile strip**  
**SLZS-40- -**  
Part number: 150919

**FESTO**



**Data sheet**

<b>Feature</b>	<b>Value</b>
Design	T-slot for proximity switch Sensor rail
Max. profile length	2800 mm
Mounting position	optional
For piston diameter	Diameter 40
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C...60 °C
Type of mounting	Via through-hole and screw
Material profile	Wrought aluminium alloy Anodised
Note on materials	RoHS-compliant
Material screws	High-alloy steel