


Flow control valve GRLO-10-UNF-1/4-B

Part number: 151571

FESTO

Without non-return function, with swivel joint.

This product is only available if ordered from the Festo Corporation, USA.



Data sheet

| Feature | Value |
|------------------------------|--|
| Valve function | Throttle function |
| Pneumatic connection, port 2 | UNF10-32 |
| Adjusting element | Slotted head screw |
| Mounting type | Threaded |
| Operating pressure | 0 ... 10 bar |
| Ambient temperature | -10 ... 60 °C |
| Operating medium | Filtered, unlubricated compressed air, 40 µm filtration Filtered, lubricated compressed air, 40 µm filtration |
| Medium temperature | -10 ... 60 °C |