


# Intermediate GRO-ZP-3-ISOB

Part number: 151707

FESTO



## Datasheet

Feature	Value
Function	Flow control
Type of mounting	Hole
Connection type I	Female thread
Connection type II	Female thread
Operating pressure min.	0 bar
Operating pressure max.	16 bar
Minimum ambient temperature	-20 Cel
Maximum ambient temperature	80 Cel
Minimum temperature of medium	-20 Cel
Maximum temperature of medium	80 Cel
Silicone status	Free
Standard nom. flow rate I->II(S) max.	1500 l/min
Standard nom. flow rate I->II(S) min	0 l/min
Medium of operation	Filtered compr. air, lubricated or unlubricated