


quick coupling plug KSS6-1/8-A

Part number: 151781
Product to be discontinued

FESTO

For self-closing quick coupling connectors.
Type to be discontinued. Available until 2018. See Support Portal for alternative products.



Data sheet

Feature	Value
Nominal size	5 mm
Operating pressure complete temperature range	-0.95 ... 12 bar
Standard nominal flow rate	963 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	-10 ... 60 °C
Authorisation	BIA TÜV
Nominal tightening torque	5 Nm
Tolerance for nominal tightening torque	± 15 %
Product weight	19 g
Pneumatic connection, port 1	Male thread G1/8
Materials note	Conforms to RoHS