

# Linear drive DGO-1/2"- -P-A-B

Part number: 15227

FESTO



## Data sheet

Feature	Value
Stroke	0.04 in...157 in
Piston diameter	1/2"
Cushioning	Elastic cushioning rings/plates at both ends
Guide	Plain-bearing guide
Operating pressure	2 bar...7 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C...60 °C
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	68 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	68 N
Pneumatic connection	10-32 UNF-2B