

**Ball valve**  
**QH-QS-4-1/8**  
Part number: 153486

**FESTO**



## Data sheet

Feature	Value
Valve function	2/2 double solenoid
Pneumatic connection, port 1	R1/8
Pneumatic connection, port 2	QS-4
Type of actuation	Manual
Type of mounting	Screw-in
Standard nominal flow rate (standardised to DIN 1343)	235 l/min
Nominal size	2.5 mm
Operating pressure	-0.1 MPa...1 MPa -1 bar...10 bar
Ambient temperature	0 °C...60 °C
Material housing	PBTP
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Sealing principle	Soft
Design	Ball valve
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	14 g
Material screwed plug	Nickel-plated brass
Note on materials	RoHS-compliant