

Push-in T-fitting QSYLV-1/2-1/2-U

Part number: 153798

FESTO



Data sheet

| Feature | Value |
|---|---|
| Size | Standard |
| Nominal size | 7.1 mm |
| Type of seal on screwed plug | Coating |
| Mounting position | optional |
| Design | L-shape, dual, parallel Push-pull principle |
| Size of pack | 1 |
| Operating pressure complete temperature range | -0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi |
| Maritime classification | See certificate |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:...] |
| Note on operating and pilot medium | Lubricated operation possible |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C...60 °C 14 °F...140 °F |
| Max. tightening torque | 30 Nm |
| Number of outputs | 2 |
| Number of supply lines | 1 |
| Type of mounting | Hollow bolt with external hex |
| Pneumatic connection, port 1 | Male thread 1/2 NPT |
| Pneumatic connection, port 2 | For tubing outside diameter of 1/2" |
| Colour of release ring | grey |
| Note on materials | RoHS-compliant |
| Material housing | PBT |
| Material release ring | POM |
| Material tubing seal | NBR |
| Material tubing clamp component | High-alloy stainless steel |