

Switch lug DASI-Q11-35/40-A-SL

Part number: 1548155

FESTO



Data sheet

| Feature | Value |
|--------------------------------|--|
| Size | 35 40 |
| Design | For T-slot |
| For piston diameter | Ø35 Diameter 40 |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C...60 °C |
| Product weight | 8 g |
| Type of mounting | Clamped in T-slot Via threaded pin Via female thread |
| Note on materials | RoHS-compliant |
| Material screws | Steel Galvanised |