

Angled plug socket MPPE-3-B

Part number: 161839

FESTO



Data sheet

| Feature | Value |
|------------------------------|--------------------------------------|
| Frequency of connection | 500 |
| Type of mounting | Via union nut |
| Mounting position | optional |
| Product weight | 65 g |
| Electrical connection | 8-pin Angled socket Solderable |
| Operational voltage range DC | 60 V |
| Permissible current load | 5 A |
| Cable fitting | Pg 9 |
| Permissible cable diameter | 6 mm...8 mm |
| Connection cross section | 0.75 mm ² |
| Degree of protection | IP67 |
| Ambient temperature | -30 °C...95 °C |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Material housing | PA |
| Housing colour | Black |
| Material union nut | PA |
| Material electrical contact | Copper Tin-plated |