


# connecting cable KVIA-MPYE-10

Part number: 161985

FESTO

for proportional valves



## Data sheet

Feature	Value
Mounting type	With sleeve nut
Assembly position	Any
Product weight	530 g
Electrical connection	Plug straight / socket straight
Operating voltage range AC	$\leq 250$ V
Permissible current load	1 A
Cable length	10 m
Cable diameter	6.2 mm
Cable structure	4x0,25
Protection class	IP65
Ambient temperature	-30 ... 80 °C
Material cable sheath	PVC
Material housing	PBT
Material electrical contact	Bronze Silver and gold plated