



Non-return valve HGL-1/8

Part number: 12938

FESTO

With sealing ring OL.

Discontinued, available through 2006



Data sheet

Feature	Value
Valve function	piloted non-return function
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 2	G1/8
Mounting type	Threaded
Standard nominal flow rate	260 l/min
Operating pressure	0.4 ... 10 bar
Operating medium	Dried, filtered compressed air Dried, filtered and lubricated compressed air
Ambient temperature	-20 ... 80 °C
Assembly position	Any
Medium temperature	-20 ... 80 °C
Max. tightening torque	12 Nm
Pilot air port 21	G1/8
Materials information for screw-in stud	Aluminium
Materials information for seals	NBR