

# Push-in connector


## QS-B-12-10-10

Part number: 130972  
Product to be discontinued

FESTO

reducing.

Type to be discontinued. Available until 2018. See Support Portal for alternative products.



## Data sheet

| Feature                                       | Value   |
|---|---|
| Size  | Standard  |
| Nominal size                                  | 6.9 mm  |
| Assembly position                             | Any   |
| Container size                                | 10  |
| Design structure                              | Push/pull principle                                     |
| Operating pressure complete temperature range | -0.95 ... 10 bar  |
| Operating medium                              | Compressed air in accordance with ISO8573-1:2010 [7::-] |
| Note on operating and pilot medium            | Lubricated operation possible                           |
| Corrosion resistance classification CRC       | 1   |
| Ambient temperature                           | -10 ... 60 °C   |
| Authorization                                 | Germanischer Lloyd                                      |
| Product weight                                | 21 g  |
| Pneumatic connection, port 1                  | For tubing outside diameter 12 mm                       |
| Pneumatic connection, port 2                  | for tubing, 10mm outside diameter                       |
| color of release ring                         | blue  |
| Materials note                                | Conforms to RoHS  |
| Materials information, housing                | PBT   |
| Release ring material data                    | POM   |
| Materials information for tubing seal         | NBR   |
| Hose clamping segment material data           | High alloy steel, non-corrosive                         |