

# Push-in connector NPQP-D-Q6-S8

Part number: 132590

FESTO

Type to be discontinued. Available until 2013.



## Data sheet

| Feature                                 | Value  |
|---|--|
| Size                                    | Standard   |
| Nominal size                            | 3.8 mm   |
| Design structure                        | Push/pull principle                                      |
| Temperature dependent working pressure  | -0.95 ... 10 bar   |
| Operating medium                        | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Note on operating and pilot medium      | Lubricated operation possible                            |
| Corrosion resistance classification CRC | 4  |
| Ambient temperature                     | -20 ... 60 °C  |
| Product weight                          | 3.2 g  |
| Pneumatic connection, port 1            | Push-in sleeve QS-8                                      |
| Pneumatic connection, port 2            | for tubing, 6mm outside diameter                         |
| Materials note                          | Contains PWIS substances<br>Conforms to RoHS             |
| Materials information, housing          | PP   |
| Hose clamping segment material data     | High alloy steel, non-corrosive                          |