

# Plastic tubing PU-2-BL

Part number: 13365

FESTO

For CN and CK connectors, particularly flexible and kink-resistant, polyurethane (not approved for use in the food industry).  
The maximum pressure value is permissible at the maximum temperature.



## Data sheet

| Feature                                | Value  |
|--|--|
| Outside diameter                       | 3.2 mm   |
| Bending radius relevant for flow rate  | 13 mm  |
| Inside diameter                        | 2.3 mm   |
| Temperature dependent working pressure | -0.95 ... 10 bar   |
| Operating medium                       | Compressed air in accordance with ISO8573-1:2010 [7::-:] |
| Ambient temperature                    | -35 ... 60 °C  |
| Authorization                          | TÜV  |
| Product weight according to length     | 0.005 kg/m   |
| Color                                  | blue   |
| Shore hardness                         | D 52 +/-3  |
| Materials note                         | Free of copper and PTFE<br>Conforms to RoHS              |
| Materials information for tubing       | TPE-U(PU)  |