


Axial kit EAMM-A-G19-40G

Part number: 1454259

FESTO

Suitable for electric drives.



Data sheet

Feature	Value
Assembly position	Any
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	1.5 Nm
Product weight	190 g
Interface code, actuator	G19
Interface code, motor in	40G
Materials note	Conforms to RoHS