


Limit switch attachment

QH-DR-E-S3-PK-3-B-B

Part number: 164855

FESTO



Data sheet

Feature	Value
Based on the standard	VDI/VDE 3845 (NAMUR)
Design	Angular
Assembly position	Any
Measuring principle	pneumatic
Switching position indicator	No
Working pressure	-0.95 ... 8 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Protection class	IP65
Ambient temperature	-10 ... 60 °C
Pneumatic connection	G1/8
Materials note	Conforms to RoHS
Materials information for seals	EPDM
Notes on materials for housing cover	PC
Notes on materials for housing socket	PA
Notes on materials for console	High alloy steel, non-corrosive