

Spiral plastic tubing PPS-6-15-1/4-CT-BL

Part number: 165872

FESTO

With 2 rotatable fittings and sealing rings, polyamide (not approved for use in the food industry).

Type to be discontinued. Available until 2011.



Data sheet

Feature	Value
Working length	15 m
Outside diameter	7.8 mm
Block length	0.8 m
Inside diameter	6.2 mm
Coil diameter	75 mm
Number of windings	86
Temperature dependent working pressure	-0.95 ... 17.2 bar
Operating medium	Filtered compressed air Vacuum
Corrosion resistance classification CRC	1
Ambient temperature	-30 ... 80 °C
Product weight	472 g
Pneumatic connection	G1/4
Color	blue
Material information, connecting thread	Wrought Aluminum alloy Anodized
Materials note	Free of copper and PTFE Conforms to RoHS
Material information, protection against kinking	Steel Galvanized
Materials information for tubing	PA-P