


# Encoder cable NEBC-S1G9-K-0.5-N-S-S1G9

Part number: 1680830

FESTO



## Data sheet

Feature	Value
Protection class	IP20
Ambient temperature with flexible cable installation	-40 ... 70 °C
Ambient temperature	-40 ... 70 °C
Min. cable bending radius	51 mm
Suitable for chain link trunking	Yes
Cable structure	Shielded 4x(2 x 0,14 mm <sup>2</sup> )
Cable length	0.5 m
Materials note	Conforms to RoHS
Materials information, cable sheaths	TPE-U(PU)