

Connecting cable KSPC-AIF-1-WD-8

Part number: 170237

FESTO

For controller axis interface.



Data sheet

Feature	Value
Operating voltage range AC	≤ 60 V
CE symbol (see declaration of conformity)	according to EU-EMV guideline
Protection class	IP20
Ambient temperature with flexible cable installation	-5 ... 80 °C
Ambient temperature	-20 ... 70 °C
Product weight	410 g
Electrical connection 1	Angled socket, M9, 5-pin, screened
Electrical connection 2	Socket strip 5-pin
Cable structure	$2 \times 0,25 \text{ mm}^2 + 2 \times 0,34 \text{ mm}^2 + 0,49 \text{ mm}^2$
Cable diameter	5.5 mm
Cable length	8 m
Housing color	Black
Cable sheath color	light grey
Materials information for locknut	Nickel-plated brass
Materials note	Conforms to RoHS
Materials information, housing	PA-reinforced PBT TPE-U(PUR)
Materials information, cable sheaths	TPE-U(PUR)
Material information for crimp connectors	Gold-plated bronze Copper alloy, tinned