


# Multi-pin socket connector IMP1-SD-72

Part number: 18319

FESTO



## Data sheet

Feature	Value
Permissible cable diameter	18 ... 27 mm
Assembly position	Any
Operating voltage range AC	≤ 300 V
Operating voltage range DC	≤ 250 V
Protection class	IP65
Ambient temperature	-40 ... 125 °C
Product weight	401 g
Terminal cross-section	1.5 mm <sup>2</sup>
Electrical connection	Plug socket 72-pin
Cable gland connection	Pg29
Mounting type	With clamp strap
Materials information, housing	Plastic Die-cast light alloy
Material information for crimp connectors	Copper alloy Silver plated