


Suction cup VAS-8-M5-NBR-CT

Part number: 183508

FESTO

With sealing ring OL.
Run-out type. Available until 2010.



Data sheet

Feature	Value
Nominal size	2 mm
suction cup diameter	8 mm
Effective suction diameter	5.5 mm
Design structure	Vacuum connection at top round, standard
Operating medium	Atmospheric air
Ambient temperature	-20 ... 80 °C
Breakaway force at 70% vacuum	1.6 N
Mounting thread	M5
suction cup mounting	M5
Vacuum connection	M5
Shore hardness	73
Materials information for screw-in stud	High alloy steel, non-corrosive
Materials note	Free of copper and PTFE
Materials information for suction cup	NBR