

# Multi-pin socket connector IMP2-SD-26-EA

Part number: 18665

FESTO



## Data sheet

Feature	Value
Permissible cable diameter	13.5 ... 15 mm
Assembly position	Any
Operating voltage range AC	$\leq 250$ V
Permissible current load	7.5 A
Protection class	IP65
Ambient temperature	-40 ... 125 °C
Product weight	97 g
Electrical connection	Plug socket 26-pin
Cable gland connection	Pg16
Plug coding	Y - for inputs/outputs
Mounting type	With sleeve nut
Materials information for seals	CR Light and oil resistant
Materials information, housing	Copper alloy Nickel plated
Material information for crimp connectors	Copper alloy Gold plated