


Decentralized controller DLP-VSE-2-5/2-0

Part number: 188466

FESTO

For DLP cylinder series.



Data sheet

Feature	Value
Mounting type	Optional with through hole with accessories
Outdoor use	C1 - weather protected locations of use
Working pressure	3 ... 8 bar
Nominal working pressure	6 bar
Operating voltage range DC	20.4 ... 28.8 V
Max. current consumption	120 mA
CE symbol (see declaration of conformity)	according to EU-EMV guideline
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Corrosion resistance classification CRC	3
Relative air humidity	5 - 100 % Condensing
Protection class	IP65 in assembled condition to IEC 60529
Ambient temperature	-5 ... 50 °C
Product weight	1,600 g
Materials information for cover	Wrought Aluminum alloy Anodized
Materials information for seals	NBR
Materials information, housing	Wrought Aluminum alloy Anodized
Screw material data	Steel Galvanized
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)