

Plastic tubing

PL-13-BL

Part number: 4103

FESTO

For CK and N connectors.

The maximum pressure value is permissible at the maximum temperature.



Data sheet

Feature	Value
Outside diameter	17.6 mm
Bending radius relevant for flow rate	100 mm
Inside diameter	13 mm
Temperature dependent working pressure	0 ... 7 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Ambient temperature	-10 ... 35 °C
Product weight according to length	0.135 kg/m
Color	blue
Shore hardness	A 85 +/-3
Materials note	Free of copper and PTFE Conforms to RoHS
Materials information for tubing	PVC-P