


Plug socket with cable KMH-D-2,5

Part number: 527398

FESTO

For valve manifold CPA-SC.



Data sheet

Feature	Value
Mounting type	Clip
Assembly position	Any
Product weight	24 g
Electrical connection	Plug socket 3-pin
Nominal operating voltage DC	60 V
Permissible current load	3 A
Cable length	2.5 m
Cable diameter	1.3 mm
Cable structure	3x0,14
Color code, core insulation	Pin 1 = black Pin 2 = blue Pin 3 = red
Protection class	IP40
Ambient temperature	-40 ... 105 °C
Materials note	Conforms to RoHS
Material cable sheath	PVC
Material housing	POM
Material electrical contact	Bronze Galvanized