

Coupling EAMC-B-15-22-5-9

Part number: 529953

FESTO

For electromechanical drive with servomotor



Data sheet

Feature	Value
Holder diameter 1	5 mm
Holder diameter 2	9 mm
Size	15
Nominal length	22 mm
Assembly position	Any
Max. speed	12,000 1/min
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 ... 60 °C
Mass moment of inertia	0.13 kgmm ²
Transferable torque	1 Nm
Product weight	6 g
Materials note	Conforms to RoHS