


Set paralel EAMM-U-60-D40-60R-91

Numar piesa: 1210446

FESTO



Fisa de date

| Caracteristica | Valoare |
|------------------------------|------------------------|
| Dimensiune | 60 |
| Pozitie de instalare | orice |
| Raportul de transmisie | 1:1 |
| Turatie max. | 6000 1/min |
| Conformitatea LABS | VDMA24364 zona III |
| Temperatura de depozitare | -25 °C...60 °C |
| Umiditate relativa | 0 - 95 % |
| Tip de protectie | IP40 |
| Temperatura ambianta | -10 °C...60 °C |
| Momentul de inertie al masei | 26.7 kgmm ² |
| Cuplu de antrenare in gol | 0.07 Nm |
| Cuplu transmisibil | 3 Nm |
| Greutate produs | 1120 g |
| Cod de interfata actuator | D40B |
| Codul interfetei motor In | 60R |
| Nota privind materialele | Conform RoHS |