


# Ventuza VAS-8-M5-S

Cod: 12612

FESTO

Niplu cu stut pentru tub plastic interior 3 mm, racordare laterala.



## Fisa tehnica

Caracteristica	valoare
deschidere nominala	2 mm
diametru ventuza	8 mm
diametru efectiv ventuza	5,5 mm
pozitia racordului	At the side
structura constructiva	racord de vacuum lateral rotund, standard
mediu de operare	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
temperatura mediului	-20 ... 60 °C
forta de rupere la 70% vacuum	1,6 N
Retention force at nominal operating pressure	1,6 N
filet de fixare	M5
fixarea ventuzei	M5
racord de vacuum	PK-3
culoare	transparent
duritate Shore	60 +/- 5
informatii referitoare la material pentru fus cu insurubare	alama
indicatie material	conform RoHS
informatii referitoare la material pentru ventuza	TPE-U(PU)