

Set fus oscilant ZNCM-40


Cod: 163526

★ Standard-Programm

Produs in retragere de pe piata

Type to be discontinued. Available until 2014. See Support Portal for alternative products.

FESTO



Fisa tehnica

Caracteristica	valoare
marime de fabricatie	40
bazat pe norme	ISO 15552 (anterior si VDMA 24652, ISO 6431, NF E49 003.1, UNI 10290)
clasa de rezistenta la coroziune KBK	1
temperatura mediului	-40 ... 150 °C
greutate produs	395,5 g
indicatie material	Free of copper and PTFE conform RoHS
informatii referitoare la material pentru suruburi	otel zincat
Trunnion flange material information	otel galvanizat
Clamping piece material information	otel galvanizat
Informatii material: Tija	otel inoxidabil inalt aliat