


Interfata CAN SPC200-COM-CAN

Cod: 194017

FESTO



Fisa tehnica

Caracteristica	valoare
sustinere configurare	date EDS
consum tipic de curent pe modul	50 mA
Simbol CE (vezi declaratia de conformitate)	conform directivei europene EMV
greutate produs	80 g
volumele de adresa maxime ale iesirilor	8 byte
volumele de adresa maxime ale intrarilor	8 byte
domeniul de adresare al interfetei bus-ului de camp	0 ... 63
varianta interfata bus de camp	izolatie galvanica layer 1 conform ISO/DIS 11898 highspeed standard pana la 1 Mbit layer 2 conform specificatiei CAN V2.0 Device Net Release 2.0 cod de produs: 9434 Device Type: Comm. Adap. (12d) 125, 250, 500 kBaud
racord electric interfata bus de camp	regleta conexiuni cu 5 poli conform CIA DR-303-1
spatiu instalare	de la 3 in sus