


Ventuza burduf VASB-8-M5-PUR

Cod: 35417

FESTO

cu inel de etansare OL.



Fisa tehnica

| Caracteristica | valoare |
|---|--|
| deschidere nominala | 2 mm |
| diametru ventuza | 8 mm |
| diametru efectiv ventuza | 5,5 mm |
| structura constructiva | racord de vacuum deschis rotund, burduf incretit de 1,5 ori |
| mediu de operare | aer atmosferic |
| temperatura mediului | -20 ... 60 °C |
| forta de rupere la 70% vacuum | 1,6 N |
| filet de fixare | M5 |
| fixarea ventuzei | M5 |
| racord de vacuum | M5 |
| duritate Shore | 62 |
| informatii referitoare la material pentru ventuza | TPE-U(PU) |