



Modul de ramificare MS4-FRM-1/8-Y-Z

Cod: 529561

FESTO

cu releu de presiune fara indicare, debit de tranzit de la dreapta la stanga.



Fisa tehnica

| Caracteristica | valoare |
|---|---|
| pozitie instalare | oricare |
| structura constructiva | modul de ramificatie |
| presiune de operare | 0 ... 12 bar |
| debit standard in directia principala de curgere 1->2 | 1.800 l/min |
| debit standard la iesirea superioara | 1.600 l/min |
| debit standard la iesirea inferioara | 1.700 l/min |
| medii de operare | Compressed air in accordance with ISO8573-1:2010 [7:4:4] Inert gases |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| clasa de rezistenta la coroziune KBK | 2 |
| temperatura de depozitare | -10 ... 60 °C |
| temperatura mediului | -10 ... 60 °C -10 ... 60 °C |
| greutate produs | 405 g |
| racord pneumatic 1 | G1/8 |
| racord pneumatic 2 | G1/8 |
| racord pneumatic 3 | G1/4 |
| racord pneumatic 4 | G1/4 |
| indicatie material | Free of copper and PTFE conform RoHS |
| informatii referitoare la material pentru carcasa | aluminu turnat sub presiune |