

Vod za programiranje KDI-MC-M8-SUB-9-2,5



Broj artikla: 537926

Komponenta koja će prestati da se proizvodi

[odgovara za MTR-DCI-...](#)

Tip se više ne proizvodi. Isporučuje se do 2020. Vidi Support Portal za alternativni proizvod.

FESTO



Tehnički podaci

Svojstvo	Vrednost
Protokol	RS232
Cable identification	sa priborom
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utikači
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	M8x1 A-coded to EN 61076-2-104
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	3
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, design	ugaono
Electrical connection 2, connection type	Utičnica
Electrical connection 2, cable outlet	Ravno
Electrical connection 2, connection technology	Sub-D
Electrical connection 2, number of pins/wires	9
Electrical connection 2, occupied pins/wires	8
Electrical connection 2, type of mounting	2x screw 4-40 UNC-2A
Područje pogonskog napona DC	0 ... 24 V
Strujna opteretivost kod 40°C	4 A
Čvrstoća na udarno naprezanje	1,5 kV
Dužina kabla	2,5 m
Svojstvo kabla	Standard
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Prečnik kabla	5 mm
Struktura kabla	3x0,25 zaslonjeno
Nazivni presek provodnika	0,25 mm ²
Mehanička zaštita	IP54
Note on degree of protection	IP40 for Sub-D socket u montiranom stanju
Temperatura okoline	0 ... 50 °C
Temperatura okoline kod pokretnog postepenja kablova	0 ... 50 °C
Materijal - napomena	Sadrži PWIS RoHS komformnost
Stepen zagađenja	2
Material cable sheath	TPE-U(PUR)
Boja izolacije	crno
Material insulation	PVC