



Fieldbus adapter FBA-PB-SUB-9-3XM12

Broj artikla: 537934

Komponenta koja će prestati da se proizvodi

[za spajanje na PROFIBUS.](#)

FESTO



Tehnički podaci

Svojstvo	Vrednost
Protokol	PROFIBUS
Electrical connection 1, function	Field device side
Electrical connection 1, design	ugaono
Electrical connection 1, connection type	Utikači
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	9
Electrical connection 1, occupied pins/wires	7
Electrical connection 1, type of mounting	2 screws 4-40 UNC
Electrical connection 2, function	Controller side Incoming bus connection (A), outgoing bus connection (B), power supply bus (C)
Electrical connection 2, design	rund (A), (B), (C)
Electrical connection 2, connection type	Plug connector (A), socket (B), plug connector (C)
Electrical connection 2, cable outlet	Straight (A), (B), (C)
Electrical connection 2, connection technology	M12x1 B(A),(B),M12x1 A(C)
Nazivni pogonski napon DC	24 V
Dužina kabela	0,11 m
Prečnik kabela	6 mm
Struktura kabela	7x0,14 zaslonjeno
Nazivni presek provodnika	0,14 mm ²
Mehanička zaštita	IP67
Note on degree of protection	u montiranom stanju
Temperatura okoline	-5 ... 50 °C
Materijal - napomena	Sadrži PWIS
Klasa korozione otpornosti KBK	0 - No corrosion stress
Material cable sheath	TPE-U(PUR)