

# Motorski vod KMTR-DC-SUB-15-M12-2,5



Broj artikla: 538917

Komponenta koja će prestati da se proizvodi

za spajanje električnog mini klizača SLTE ili paralelne hvataljke HGPLE sa upravljačkom jedinicom za motor SFC-DC.

Tip se više ne proizvodi. Isporučuje se do 2020. Vidi Support Portal za alternativni proizvod.

FESTO



## Tehnički podaci

Svojstvo	Vrednost
Cable identification	sa priborom
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	M12x1 A-coded to EN 61076-2-101
Electrical connection 1, number of pins/wires	12
Electrical connection 1, occupied pins/wires	11
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, design	ugaono
Electrical connection 2, connection type	Utikači
Electrical connection 2, cable outlet	Ravno
Electrical connection 2, connection technology	Sub-D
Electrical connection 2, number of pins/wires	15
Electrical connection 2, occupied pins/wires	11
Electrical connection 2, type of mounting	2x screw 4-40 UNC-2A
Područje pogonskog napona DC	0 ... 24 V
Strujna opteretivost kod 40°C	1 A
Čvrstoća na udarno naprezanje	0,5 kV
Dužina kabela	2,5 m
Svojstvo kabela	prikladno za energetski lanac
Bending radius, fixed cable installation	≥ 50 mm
Bending radius, flexible cable installation	≥ 80 mm
Prečnik kabela	8 mm
Struktura kabela	4x(2x0,14)D+3x0,14 zaslonjeno
Nazivni presek provodnika	0,14 mm <sup>2</sup>
Mehanička zaštita	IP67
Note on degree of protection	u montiranom stanju
Temperatura okoline kod pokretnog postepenja kablova	-25 ... 70 °C
Materijal - napomena	Sadrži PWIS RoHS komfornost
Stepen zagađenja	2
Klasa korozione otpornosti KBK	0 - No corrosion stress
Material cable sheath	TPE-U(PUR)
Boja izolacije	narandžasto