



- Compact
- Functional
- Multiple variants
- Versatile


Drive/gripper connectors

Selection aid

FESTO

Adapter kits provide a fast and simple connection between Festo grippers and drives.

The scope of delivery includes the necessary accessories such as bolts, centring discs, sleeves or pins and nuts.



Possible combinations					
	HMP, HME 	HMPL 	DGSL 	SLT, SLTE 	DGPL/DGE-KF 
2-jaw parallel gripper					
HGPT 	→ 5 / 3.2-46	→ 5 / 3.2-58	→ 5 / 3.2-65	→ 5 / 3.2-69	–
HGPL 	→ 5 / 3.2-47	→ 5 / 3.2-59	→ 5 / 3.2-66	→ 5 / 3.2-70	→ 5 / 3.2-75
HGPP 	→ 5 / 3.2-48	→ 5 / 3.2-60	→ 5 / 3.2-67	→ 5 / 3.2-71	→ 5 / 3.2-76
HGP 	→ 5 / 3.2-52	→ 5 / 3.2-61	→ 5 / 3.2-68	→ 5 / 3.2-72	→ 5 / 3.2-80
HGPC 	→ 5 / 3.2-54	→ 5 / 3.2-62	–	→ 5 / 3.2-73	–
HGPM 	–	–	–	–	–
3-jaw parallel gripper					
HGDT 	→ 5 / 3.2-55	→ 5 / 3.2-63	–	→ 5 / 3.2-74	–
HGD 	→ 5 / 3.2-50	→ 5 / 3.2-61	–	–	→ 5 / 3.2-78


Drive/gripper connectors

Selection aid

FESTO

Adapter kits provide a fast and simple connection between Festo grippers and drives.

The scope of delivery includes the necessary accessories such as bolts, centring discs, sleeves or pins and nuts.



Possible combinations					
	DGEA	DRQD	DSL-...-KF	DSM	DPZ
2-jaw parallel gripper					
HGPT	–	→ 5 / 3.2-83	–	–	–
HGPL	→ 5 / 3.2-75	→ 5 / 3.2-84	–	–	–
HGPP	→ 5 / 3.2-76	→ 5 / 3.2-87	→ 5 / 3.2-95	→ 5 / 3.2-95	–
HGP	→ 5 / 3.2-80	→ 5 / 3.2-89	→ 5 / 3.2-97	→ 5 / 3.2-97	→ 5 / 3.2-99
HGPC	–	→ 5 / 3.2-92	–	–	–
HGPM	–	→ 5 / 3.2-93	–	–	–
3-jaw parallel gripper					
HGDT	–	→ 5 / 3.2-94	–	–	–
HGD	→ 5 / 3.2-78	→ 5 / 3.2-89	→ 5 / 3.2-89	→ 5 / 3.2-89	–


Drive/gripper connectors

Selection aid

FESTO

Adapter kits provide a fast and simple connection between Festo grippers and drives.

The scope of delivery includes the necessary accessories such as bolts, centring discs, sleeves or pins and nuts.



Possible combinations					
	HMP, HME 	HMPL 	DGSL 	SLT, SLTE 	DGPL/DGE-KF 
2-jaw angle gripper					
HGW 	→ 5 / 3.2-52	→ 5 / 3.2-61	→ 5 / 3.2-68	→ 5 / 3.2-72	→ 5 / 3.2-80
HGR 	→ 5 / 3.2-52	→ 5 / 3.2-61	→ 5 / 3.2-68	→ 5 / 3.2-72	→ 5 / 3.2-80
HGWM 	–	–	–	–	–
Swivel/gripper unit					
HGDS 	→ 5 / 3.2-56	→ 5 / 3.2-64	–	–	→ 5 / 3.2-82


Drive/gripper connectors

Selection aid

FESTO

Adapter kits provide a fast and simple connection between Festo grippers and drives.

The scope of delivery includes the necessary accessories such as bolts, centring discs, sleeves or pins and nuts.



Possible combinations					
	DGEA	DRQD	DSL-...-KF	DSM	DPZ
					
2-jaw angle gripper					
HGW 	→ 5 / 3.2-80	→ 5 / 3.2-89	→ 5 / 3.2-97	→ 5 / 3.2-97	→ 5 / 3.2-99
HGR 	→ 5 / 3.2-80	→ 5 / 3.2-89	→ 5 / 3.2-97	→ 5 / 3.2-97	→ 5 / 3.2-99
HGWM 	–	→ 5 / 3.2-93	–	–	–
Swivel/gripper unit					
HGDS 	→ 5 / 3.2-82	–	–	–	–

HMP, HME/HGPT combination

Technical data

FESTO


Adapter kit HAPG

Material:

Wrought aluminium alloy, anodised

Centring pins/sleeves: High-alloy steel

Free of copper, PTFE and silicone



HMP, HME

HAPG


HGPT

Direct mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



Drive	Gripper	B1	D1	D2	H1	L1	Part No.	Type
HMP/HME-16 ¹⁾	HGPT-25	14	M4	M5	36	76	537 178	HAPG-81
HMP-20 HMP/HME-25 ¹⁾	HGPT-35	12	M4	M6	54	100	537 172	HAPG-77
HMP-20 HMP/HME-25 ¹⁾	HGPT-40	12	M6	M6	80	88.5	537 182	HAPG-84
HMP/HME-25 ¹⁾ HMP-32	HGPT-50	15	M6	M6	60	110	537 185	HAPG-86
HMP-32	HGPT-63	15	M4	M6	72	131.5	537 187	HAPG-87

1) HME: Horizontal mounting position, vertical on request

HMP, HME/HGPL combination

Technical data

FESTO

System components
Adapters

3.2


Adapter kit HAPG

Material:

Wrought aluminium alloy, anodised

Centring sleeves: High-alloy steel

Free of copper, PTFE and silicone




Direct mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



Drive	Gripper	B1	D1	D2	H1	L1	Part No.	Type
HMP/HME-16 ¹⁾ HMP-20	HGPL-14	–	–	–	–	–	–	2x M5x25 DIN 912 2x ZBH-9
HMP-20 HMP/HME-25 ¹⁾	HGPL-25	14	M5	M5	50	110	539 887	HAPG-92
HMP/HME-25 ¹⁾ HMP-32	HGPL-40	20	M8	M5	60	120	537 312	HAPG-SD2-30

1) HME: Horizontal mounting position, vertical on request


HMP, HME/HGPP combination

Technical data


FESTO

Adapter kit HAPG, HMSV

Material:
Wrought aluminium alloy, anodised
Centring pins/sleeves: High-alloy steel
Free of copper, PTFE and silicone



Direct mounting




Dovetail mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



Drive	Gripper	B1	D1	D2	H1	H2	L1	Part No.	Type
HMP/HME-16 ¹⁾	HGPP-12	20	M3	M5	85	9.5	44	191 262	HAPG-44
HMP/HME-16 ¹⁾	HGPP-16	20	M3	M5	85	9.5	44	191 263	HAPG-45
HMP-20 HMP/HME-25 ¹⁾	HGPP-16	20	M3	M5	100.4	4.7	51	191 264	HAPG-46
HMP/HME-25 ¹⁾	HGPP-20	12	M4	M5	110	7	50	191 265	HAPG-47
HMP/HME-25 ¹⁾	HGPP-25	18	M5	M5	110	–	60	529 019	HAPG-59
HMP-32	HGPP-32	18	M5	M5	133	–	60	529 020	HAPG-61

1) HME: Horizontal mounting position, vertical on request

HMP, HME/HGPP combination


Technical data

FESTO

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Dovetail mounting



Drive	Gripper	B1	D1	D2	H1	H2	H3	L1	L2	Part No.	Type
HMP/HME-16 ¹⁾	HGPP-12	30	M3	M5	51	46	44	100	85	191 262 177 649	HAPG-44 HMSV-3
HMP/HME-16 ¹⁾	HGPP-16	30	M3	M5	51	46	44	100	85	191 263 177 649	HAPG-45 HMSV-3
HMP-20 HMP/HME-25 ¹⁾	HGPP-16	30	M3	M5	51	46	51	120	100.4	191 264 177 653	HAPG-46 HMSV-7
HMP/HME-25 ¹⁾	HGPP-20	22	M4	M5	51	46	50	120	110	191 265 177 653	HAPG-47 HMSV-7
HMP/HME-25 ¹⁾	HGPP-25	28	M5	M5	51	46	60	120	110	529 019 177 653	HAPG-59 HMSV-7
HMP-32	HGPP-32	28	M5	M5	51	46	60	120	133	529 020 177 653	HAPG-61 HMSV-7

System components
Adapters

3.2


HMP, HME/HGD combination

Technical data


FESTO

Adapter kit HMSV

Material:
Wrought aluminium alloy, anodised
Centring pins/sleeves: High-alloy steel
Free of copper, PTFE and silicone



Direct mounting




Dovetail mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



- 1 Drive
- 2 Gripper
- 3 Adapter plate HMSV

Drive	Gripper	B1	D1	D2	L1	H1	L3	Part No.	Type
HMP/HME-16 ¹⁾	HGD-32	50	M3	M5	85	12	9.5	177 765	HMSV-25
HMP-20							4.5		
HMP/HME-25 ¹⁾									
HMP/HME-25 ¹⁾	HGD-50	70	M5	M5	110	14	10	177 766	HMSV-26
HMP-32							–		

1) HME: Horizontal mounting position, vertical on request

HMP, HME/HGD combination


Technical data

FESTO

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Dovetail mounting



- 1 Drive
- 2 Gripper
- Adapter kit, comprising:
- 3 Adapter plate HMSV
- 4 Dovetail clamp HMSV

Drive	Gripper	B1	B2	B3	D1	L1	L2	H1	Part No.	Type
HMP/HME-16 ¹⁾ HMP-20 HMP/HME-25	HGD-32	50	51	46	M3	85	80	22	178 212	HMSV-32
HMP/HME-25 ¹⁾ HMP-32	HGD-50	70	51	46	M5	110	100	24	178 213	HMSV-33

1) HME: Horizontal mounting position, vertical on request

System components
Adapters

3.2

HMP, HME/HGP, HGR, HGW combination

Technical data

FESTO


Adapter kit HMSV

Material:


Wrought aluminium alloy, anodised

Centring sleeves: High-alloy steel

Free of copper, PTFE and silicone



Direct mounting




Dovetail mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



- 1 Drive
- 2 Gripper
- 3 Adapter plate HMSV

Drive	Gripper	B1	D1	D2	L1	H1	L3	Part No.	Type
HMP/HME-16 ¹⁾ HMP-20	HGP-10 HGR-16 HGW-16	40	M3	M5	85	12	9.5	177 666	HMSV-20
HMP/HME-16 ¹⁾ HMP-20 HMP/HME-25 ¹⁾	HGP-16 HGP-20 HGR-25 HGW-25	40	M4	M5	85	12	9.5	177 761	HMSV-21
HMP/HME-16 ¹⁾ HMP-20 HMP/HME-25 ¹⁾ HMP-32	HGP-25 HGR-32 HGW-32	50	M6	M5	100	14	9.5	177 762	HMSV-22
HMP/HME-25 ¹⁾	HGP-35 HGR-40 HGW-40	60	M8	M5	110	18	17	177 763	HMSV-23
HMP-32	HGP-35 HGR-40 HGW-40	60	M8	M5	133	18	10.5	177 764	HMSV-24

1) HME: Horizontal mounting position, vertical on request

HMP/HGP, HGR, HGW combination


Technical data

FESTO

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Dovetail mounting



- 1 Drive
- 2 Gripper
- Adapter kit, comprising:
- 3 Adapter plate HMSV
- 4 Dovetail clamp HMSV

Drive	Gripper	B1	B2	B3	D1	L1	L2	H1	Part No.	Type
HMP-16 HMP-20	HGP-10 HGR-16 HGW-16	40	51	46	M3	85	80	22	177 767	HMSV-27
HMP-16 HMP-20 HMP-25	HGP-16 HGR-25 HGW-25	40	51	46	M4	85	80	24	177 768	HMSV-28
HMP-16 HMP-20 HMP-25 HMP-32	HGP-25 HGR-32 HGW-32	50	51	46	M6	100	100	24	177 769	HMSV-29
HMP-25	HGP-35 HGR-40 HGW-40	60	51	46	M8	110	100	28	177 770	HMSV-30
HMP-32	HGP-35 HGR-40 HGW-40	60	51	46	M8	133	100	28	178 211	HMSV-31

System components
Adapters

3.2

HMP, HME/HGPC combination

Technical data

FESTO


Adapter kit HAPG

Material:

Wrought aluminium alloy, anodised

Centring sleeves: High-alloy steel


Free of copper, PTFE and silicone



Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



Drive	Gripper	B1	D1	D2	H1	L1	Part No.	Type
HMP/HME-16 ¹⁾	HGPC-16	20	M5	M5	44	85	191 263	HAPG-45
HMP-20	HGPC-20	20	M6	M5	51	100.4	191 264	HAPG-46
HMP/HME-25 ¹⁾								

1) HME: Horizontal mounting position, vertical on request

HMP, HME/HGDT combination

Technical data

FESTO

System components
Adapters

3.2


Adapter kit HAPG

Material:

Wrought aluminium alloy, anodised

Centring pins/sleeves: High-alloy steel

Free of copper, PTFE and silicone




Direct mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



Drive	Gripper	B1	D1	D2	L1	Part No.	Type
HMP/HME-16 ¹⁾	HGDT-35	50	M3	M5	11.5	542 434	HAPG-98
HMP/HME-16 HMP-20 HMP/HME-25	HGDT-40	74	M5	M5	12.5	542 437	HAPG-95
HMP-20 HMP/HME-25 HMP-32	HGDT-50	92	M6	M5	11.5	542 443	HAPG-SD2-36
HMP/HME-25 HMP-32	HGDT-63	114	M6	M5	11.5	542 438	HAPG-96

1) HME: Horizontal mounting position, vertical on request


HMP, HME/HGDS combination

Technical data




Adapter kit HMSV, connecting kit HAVB

Material:
Wrought aluminium alloy, anodised
Centring sleeves: High-alloy steel
Free of copper, PTFE and silicone



Direct mounting




Dovetail mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



- 1 Drive
- 2 Swivel/gripper unit
- 3 Adapter kit HMSV

Drive	Gripper	Part No.	Type
HMP/HME-16 ¹⁾	HGDS-12	534 290	HMSV-38
HMP-20	HGDS-16		
HMP/HME-25 ¹⁾	HGDS-20		
HMP-32			

1) HME: Horizontal mounting position, vertical on request

HMP, HME/HGDS combination

Technical data



Dimensions and ordering data
Download CAD data → www.festo.com/en/engineering

Dovetail mounting

1

 Drive

2

 Swivel/gripper unit

3

 Adapter kit HMSV

4

 Adapter kit HAVB

Drive	Gripper	Part No.	Type
HMP/HME-16 ¹⁾	HGDS-12	534 290	HMSV-38
HMP-20	HGDS-16	163 239	HAVB-3
HMP/HME-25 ¹⁾	HGDS-20		
HMP-32			

1) HME: Horizontal mounting position, vertical on request

HMPL/HGPT combination

Technical data




Adapter kit HAPG

Material:

Wrought aluminium alloy, anodised

Centring pins/sleeves: High-alloy steel

Free of copper, PTFE and silicone




Direct mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



Drive	Gripper	B1	D1	D2	H1	L1	Part No.	Type
HMPL-12 HMPL-16	HGPT-16	12	M2	M5	24	35.8	537 167	HAPG-73
HMPL-12 HMPL-16	HGPT-20	12	M3	M5	28	44	537 176	HAPG-80
HMPL-16	HGPT-25	14	M4	M5	45	64	537 179	HAPG-82
HMPL-20	HGPT-25 HGPT-35	12	M4	M5	28	44	537 174	HAPG-78


HMPL/HGPL combination

Technical data




Adapter kit HAPG

Material:
Wrought aluminium alloy, anodised
Centring sleeves: High-alloy steel
Free of copper, PTFE and silicone



Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering



Drive	Gripper	B1	D1	D2	H1	L1	Part No.	Type
HMPL-16	HGPL-14	12	M4x30	M5x20	50	71	539 912	HAPG-93
HMPL-20								


HMPL/HGPP combination

Technical data

FESTO

Adapter kit HAPG

Material:
Wrought aluminium alloy, anodised
Centring pins/sleeves: High-alloy steel
Free of copper, PTFE and silicone



Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering



Drive	Gripper	B1	D1	D2	H1	L1	Part No.	Type
HMPL-12 HMPL-16	HGPP-12	12	M3	M5	38	39.5	191 899	HAPG-53
HMPL-12 HMPL-16	HGPP-10	12	M3	M5	42	38	529 016	HAPG-56
HMPL-20	HGPP-12	12	M3	M5	52	44	191 900	HAPG-54
HMPL-20	HGPP-16	12	M3	M5	62	40	191 901	HAPG-55

HMPL/HGP, HGD, HGW, HGR combination

FESTO

Technical data


Adapter kit HAPG

Material:

Wrought aluminium alloy, anodised

Centring pins/sleeves: High-alloy steel


Free of copper, PTFE and silicone



Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



Drive	Gripper	D1	D2	H1	L1	Part No.	Type
HMPL-12	HGP-10 HGR-16 HGW-16	M3	M5	30	30	192 708	HAPG-39-S1
HMPL-12	HGP-06 HGR-10 HGW-10	M3	M5	30	30	192 709	HAPG-60-S1
HMPL-16 HMPL-20	HGP-10 HGR-16 HGW-16	M3	M5	42	50	192 705	HAPG-36-S1
HMPL-16 HMPL-20	HGD-16	M3	M5	42	50	193 921	HAPG-36-S3
HMPL-16 HMPL-20	HGP-06 HGR-10 HGW-10	M3	M5	42	50	192 706	HAPG-37-S1
HMPL-16 HMPL-20	HGP-16 HGP-20 HGR-25 HGW-25	M4	M5	42	50	193 922	HAPG-37-S4

HMPL/HGPC combination

Technical data

FESTO


Adapter kit HAPG

Material:


Wrought aluminium alloy, anodised

Centring sleeves: High-alloy steel

Free of copper, PTFE and silicone



Direct mounting




Direct mounting

Dimensions and ordering data


Download CAD data → www.festo.com/en/engineering

Direct mounting with HAPG-55



Drive	Gripper	B1	D1	D2	H1	L1	Part No.	Type
HMPL-16	HGPC-16	12	M5	M5	40	62	191 901	HAPG-55
HMPL-20								
HMPL-20	HGPC-20	12	M6	M5	40	62		

Direct mounting with HAPG-100



Drive	Gripper	B1	D1	D2	D3	H1	L1	Part No.	Type
HMPL-12	HGPC-12	10	M4	M5	M4	43	49	542 670	HAPG-100
HMPL-16									

HMPL/HGDT combination

Technical data

FESTO

System components
Adapters

3.2


Adapter kit HAPG

Material:

Wrought aluminium alloy, anodised

Centring pins/sleeves: High-alloy steel

Free of copper, PTFE and silicone




Direct mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



Drive	Gripper	B1	D1	D2	L1	Part No.	Type
HMPL-12 HMPL-16	HGDT-25	49	M3	M5	8.5	542 433	HAPG-97
HMPL-20	HGDT-35	58	M3	M5	8.5	542 435	HAPG-99
HMPL-20	HGDT-40	74	M5	M5	12.5	542 437	HAPG-95

HMPL/HGDS combination


Technical data

FESTO

Adapter kit

(user configured)

Material:
to DIN 912
Centring sleeves: High-alloy steel
Free of copper, PTFE and silicone




Direct mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



Drive	Gripper	Part No.	Type
HMPL-12	HGDS-12	–	2x M5x18 DIN 912
HMPL-16			2x ZBH-9
HMPL-16	HGDS-16	–	2x M5x18 DIN 912
HMPL-20	HGDS-20		2x ZBH-9

DGSL/HGPT combination

Technical data

FESTO

System components
Adapters

3.2


Adapter kit HAPG

Material:

Wrought aluminium alloy, anodised

Centring pins/sleeves: High-alloy steel

Free of copper, PTFE and silicone




Direct mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



Drive	Gripper	B1	D1	D2	H1	L1	Part No.	Type
DGSL-8/10	HGPT-16	27	M4	M2.5	8	49.6	537 169	HAPG-75
	HGPT-20			M3				
DGSL-12/16	HGPT-16	33	M5	M2.5	10	65.6	537 170	HAPG-76
	HGPT-20			M3				
DGSL-12/16	HGPT-25	38	M5	M4	10	65.6	537 180	HAPG-83
DGSL-20/25	HGPT-25/35	45	M6	M4	10	84.6	537 175	HAPG-79
DGSL-20/25	HGPT-40	57	M6	M5	12	103.6	537 183	HAPG-85

DGSL/HGPL combination

Technical data

FESTO


Adapter kit HAPG

Material:

Wrought aluminium alloy, anodised

Centring pins/sleeves: High-alloy steel

Free of copper, PTFE and silicone




Direct mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



- 1 Drive
- 2 Gripper
- 3 Adapter plate HAPG

Drive	Gripper	B1	D1	D2	H1	L1	Part No.	Type
DGSL-16	HGPL-14	44	M5	M4	14	75	538 055	HAPG-89
DGSL-20/25	HGPL-14	52	M6		13.5	90	539 274	HAPG-90
DGSL-25	HGPL-25							

DGSL/HGPP combination

Technical data

FESTO

System components
Adapters

3.2


Adapter kit HAPG

Material:

Wrought aluminium alloy, anodised

Centring pins/sleeves: High-alloy steel

Free of copper, PTFE and silicone




Direct mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



Drive	Gripper	B1	D1	D2	H1	L1	Part No.	Type
DGSL-8/10	HGPP-10	33	M4	M3	8	49.6	526 017	HAPG-57
DGSL-12/16	HGPP-10		M5			65	529 018	HAPG-58
DGSL-12/16	HGPP-12	36			M6	10	80	191 266
DGSL-20/25	HGPP-12	44	12			91	191 267	HAPG-49
DGSL-20/25	HGPP-16			191 269			HAPG-51	
DGSL-20/25	HGPP-20	58	M4	191 270		HAPG-52		

DGSL/HGP, HGW, HGR combination

Technical data

FESTO


Adapter kit HMSV

Material:

Wrought aluminium alloy, anodised

Centring pins/sleeves: High-alloy steel

Free of copper, PTFE and silicone




Direct mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



- 1 Drive
- 2 Gripper
- 3 Adapter plate HMSV

Drive	Gripper	B1	D1	D2	H1	L1	Part No.	Type
DGSL-4/6	HGP-6	17	M3	M3	8	40	548 783	HMSV-53
DGSL-8/10	HGP-10 HGR-10 HGW-10	33	M4	M3	9	50	548 784	HMSV-54
DGSL-12/16	HGP-16	43.5	M6	M4	10	50	548 785	HMSV-55
	HGR-16 HGW-16			M3				
DGSL-20/25	HGP-20 HGR-25 HGW-25	73	M6	M4	12	100	548 786	HMSV-56
	HGP-25 HGR-32 HGW-32			M6				

SLT, SLTE/HGPT combination

Technical data

FESTO


Adapter kit HAPG

Material:

Wrought aluminium alloy, anodised

Centring pins/sleeves: High-alloy steel

Free of copper, PTFE and silicone




Direct mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



Drive	Gripper	B1	D1	D2	H1	L1	Part No.	Type
SLT-6	HGPT-16	6	M2	M3	24	38.6	537 168	HAPG-74
SLT/SLTE-10	HGPT-16	8	M2	M3	27	49.6	537 169	HAPG-75
	HGPT-20		M3					
SLT/SLTE-16	HGPT-16	10	M2	M5	33	65.6	537 170	HAPG-76
	HGPT-20		M3					
SLT/SLTE-16	HGPT-25	10	M4	M5	38	65.6	537 180	HAPG-83
SLT-20	HGPT-25	10	M4	M5	45	84.6	537 175	HAPG-79
	HGPT-35							
SLT-25	HGPT-35	12	M4	M6	54	100	537 172	HAPG-77
SLT-25	HGPT-40	12	M5	M6	57	103.6	537 183	HAPG-85

SLT, SLTE/HGPL combination

Technical data

FESTO


Adapter kit HAPG

Material:

Wrought aluminium alloy, anodised

Centring sleeves: High-alloy steel


Free of copper, PTFE and silicone



Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



Drive	Gripper	B1	D1	D2	H1	L1	Part No.	Type
SLT/SLTE-16	HGPL-14 ¹⁾	14	M4	M5	44	75	538 055	HAPG-89
SLT-20 SLT-25	HGPL-14 HGPL-25 ¹⁾	13.5	M4	M5	52	90	539 274	HAPG-90

1) Only in combination with mini slide SLT-...-CC-B (with adjustable shock absorbers) or mini slide SLTE

SLT, SLTE/HGPP combination

Technical data

FESTO


Adapter kit HAPG

Material:

Wrought aluminium alloy, anodised

Centring pins/sleeves: High-alloy steel

Free of copper, PTFE and silicone




Direct mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



Drive	Gripper	B1	D1	D2	H1	L1	Part No.	Type
SLT/SLTE-10	HGPP-10	8	M3	M4	33	49.6	529 017	HAPG-57
SLT/SLTE-16	HGPP-10	8	M3	M5	33	65	529 018	HAPG-58
SLT/SLTE-16	HGPP-12	8	M3	M5	36	65	191 266	HAPG-48
SLT-20	HGPP-12	10	M3	M5	44	80	191 267	HAPG-49
SLT-20	HGPP-16	10	M3	M5	44	80	191 268	HAPG-50
SLT-25	HGPP-16	12	M3	M6	58	91	191 269	HAPG-51
SLT-25	HGPP-20	12	M4	M6	58	91	191 270	HAPG-52

SLT, SLTE/HGP, HGW, HGR combination

Technical data

FESTO


Adapter kit HAPS

Material:

Wrought aluminium alloy, anodised

Centring pins/sleeves: High-alloy steel

Free of copper, PTFE and silicone




Direct mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



- 1 Drive
- 2 Gripper
- 3 Adapter kit

Drive	Gripper	B1	D1	D2	H1	L1	Part No.	Type
SLT-6	HGP-6	16	M3	M3	8	36	178 447	HAPS-1
SLT/SLTE-10	HGR-10 HGW-10	28	M4	M3	8	48	178 448	HAPS-2
SLT/SLTE-16	HGP-10 HGR-16 HGW-16	32	M5	M3	8	65	178 449	HAPS-3
SLT-20	HGP-16 HGP-20 HGR-25 HGW-25	44	M5	M5	10	80	178 450	HAPS-4
SLT-25	HGP-25 HGR-32 HGW-32	58	M6	M6	12	91	178 451	HAPS-5

SLT, SLTE/HGPC combination

Technical data

FESTO

System components
Adapters

3.2


Adapter kit HAPG

Material:


Wrought aluminium alloy, anodised

Centring sleeves: High-alloy steel

Free of copper, PTFE and silicone



Direct mounting




Direct mounting

Dimensions and ordering data


Download CAD data → www.festo.com/en/engineering

Direct mounting with HAPG-49/-51/-58



Drive	Gripper	B1	D1	D2	H1	L1	Part No.	Type
SLT/SLTE-16	HGPC-12	8	M4	M5	33	65	529 018	HAPG-58
SLT-20	HGPC-16	10	M5	M5	44	80	191 267	HAPG-49
SLT-25	HGPC-20	12	M6	M6	58	91	191 269	HAPG-51

Direct mounting with HAPG-100/-101/-102



Drive	Gripper	B1	D1	D2	D3	H1	L1	Part No.	Type
SLT/SLTE-10	HGPC-12	10	M4	M4	M4	43	49	542 670	HAPG-100
SLT/SLTE-16	HGPC-16	10	M5	M5	M4	33	65	542 666	HAPG-101
SLT-20	HGPC-20	10	M6	M5	M4	44	80	542 667	HAPG-102

SLT, SLTE/HGDT combination

Technical data

FESTO


Adapter kit HAPG

Material:

Wrought aluminium alloy, anodised

Centring pins/sleeves: High-alloy steel

Free of copper, PTFE and silicone




Direct mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



Drive	Gripper	B1	D1	D2	L1	Part No.	Type
SLT/SLTE-16	HGDT-25	49	M3	M4	8.5	542 433	HAPG-97
SLT/SLTE-16	HGDT-35	58	M3	M4	8.5	542 435	HAPG-99
SLT-20	HGDT-25	49	M3	M5	10	542 439	HAPG-SD2-32
SLT-20	HGDT-35	58	M3	M5	11	542 436	HAPG-94
SLT-25				M6			
SLT-20	HGDT-40	74	M5	M5	12.5	542 437	HAPG-95
SLT-25				M6			
SLT-25	HGDT-63	92	M6	M6	11.5	542 443	HAPG-SD2-36

DG.../HGPL combination

Technical data

FESTO


Adapter kit HMVA, HAPG, HMSV

Material:

Wrought aluminium alloy, anodised

Centring sleeves: High-alloy steel

Free of copper, PTFE and silicone




Dovetail mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Dovetail mounting



- 1 Linear drive
- 2 Gripper
- 3 Adapter kit HAPG
- 4 Adapter kit HMSV
- 5 Adapter kit HMVA

Drive	Gripper	Part No.	Type
DG...-40	HGPL-25	196 790	HMVA-DLA40
		177 653	HMSV-7
		539 887	HAPG-92

DG.../HGPP combination

Technical data

FESTO


Adapter kit HMVA, HAPG, HMSV

Material:

Wrought aluminium alloy, anodised

Centring pins/sleeves: High-alloy steel

Free of copper, PTFE and silicone




Dovetail mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Dovetail mounting



- 1 Linear drive
- 2 Gripper
- 3 Adapter kit HAPG
- 4 Adapter kit HMSV
- 5 Adapter kit HMVA

Drive	Gripper	B1	H1	H2	L1	L2	Part No.	Type	Part No.	Type
DGP...-25	HGPP-12	44	30	14	85	100	191 262	HAPG-44	196 788	HMVA-DLA18/25
DGE-25									177 649	HMSV-3
DGEA-18	HGPP-16	44	30	14	100	100	191 263	HAPG-45		
DGP...-32	HGPP-16	51	30	18	100	120	191 264	HAPG-46	196 789	HMVA-DL32
									177 653	HMSV-7
DGP...-40	HGPP-16	51	30	18	100	120	191 264	HAPG-46	196 790	HMVA-DLA40
DGE-40	HGPP-20	50	22	18	110	120	191 265	HAPG-47	177 653	HMSV-7
	HGPP-25	60	28	18	110	120	529 019	HAPG-59		
	HGPP-32	60	28	18	133	120	529 020	HAPG-61		


DG.../HGD combination

Technical data

FESTO

Adapter kit HMVA, HAPG, HMSV

Material:
Wrought aluminium alloy, anodised
Centring pins/sleeves: High-alloy steel
Free of copper, PTFE and silicone




DGPL
DGPIL
DGE-KF
DGE-RF
DGEA

HMVA

HAPG

HGD

Direct mounting



DGPL
DGPIL
DGE-KF
DGE-RF
DGEA

HMVA

HMSV

HMSV


HGD

Dovetail mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting



- 1 Linear drive
- 2 Gripper
- 3 Adapter kit HAPG
- 4 Adapter kit HMVA

Drive	Gripper	B1	H2	L1	Part No.	Type
DGP...-25	HGD-16	50	14	50	196 788	HMVA-DLA18/25
DGE-25					193 921	HAPG-36-S3
DGEA-18						
DGP...-32	HGD-16	60	18	74	196 789	HMVA-DL32
					193 921	HAPG-36-S3
DGP...-40	HGD-16	60	18	74	196 790	HMVA-DLA40
DGE-40					193 921	HAPG-36-S3

DG.../HGD combination


Technical data

FESTO

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Dovetail mounting



- 1 Linear drive
- 2 Gripper
- 3 Adapter kit HMSV
- 4 Adapter kit HMVA

Drive	Gripper	B1	H1	L1	L2	Part No.	Type
DG...-32	HGD-32	50	22	85	80	196 789 178 212	HMVA-DL32 HMSV-32
DGP...-40 DGE-40 DGEA-40	HGD-32	70	24	110	100	196 790 178 212	HMVA-DLA40 HMSV-32
DGP...-40 DGE-40 DGEA-40	HGD-50	70	24	110	100	196 790 178 213	HMVA-DLA40 HMSV-33

System components
Adapters

3.2


DG.../HGP, HGW, HGR combination

Technical data

FESTO

Adapter kit HMVA, HAPG, HMSV

Material:
Wrought aluminium alloy, anodised
Centring sleeves: High-alloy steel
Free of copper, PTFE and silicone




DGPL
DGPIL
DGE-KF
DGE-RF
DGEA

HMVA

HAPG

HGP

Direct mounting



DGPL
DGPIL
DGE-KF
DGE-RF
DGEA

HMVA

HMSV
HMSV


HGP

Dovetail mounting

Dimensions

Download CAD data → www.festo.com/en/engineering

Direct mounting



- 1 Linear drive
- 2 Gripper
- 3 Adapter kit HAPG
- 4 Adapter kit HMVA

Drive	Gripper	B2	H2	L2	Part No.	Type	Part No.	Type
DGP...-25	HGP-06	50	14	50	196 788	HMVA-DLA18/25	192 706	HAPG-37-S1
DGE-25	HGR-10							
DGEA-18	HGW-10							
DGP...-32		60	18	74	196 789	HMVA-DL32		
DGP...-40		60	18	74	196 790	HMVA-DLA40		
DGE-40								
DGP...-25	HGP-10	50	14	50	196 788	HMVA-DLA18/25	192 705	HAPG-36-S1
DGE-25	HGR-16							
DGEA-18	HGW-16							
DGP...-32		60	18	74	196 789	HMVA-DL32		
DGP...-40		60	18	74	196 790	HMVA-DLA40		
DGE-40								
DGP...-25	HGP-16	50	14	50	196 788	HMVA-DLA18/25	193 922	HAPG-37-S4
DGE-25	HGR-25							
DGEA-18	HGW-25							
DGP...-32		60	18	74	196 789	HMVA-DL32		
DGP...-40		60	18	74	196 790	HMVA-DLA40		
DGE-40								

DG.../HGP, HGW, HGR combination


Technical data

FESTO

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Dovetail mounting



- 1 Linear drive
- 2 Gripper
- 3 Adapter kit HMSV
- 4 Adapter kit HMVA

Drive	Gripper	B1	H1	H2	L1	L2	Part No.	Type	Part No.	Type
DGP...-25	HGP-10	40	22	14	85	80	196 788	HMVA-DLA18/25	177 767	HMSV-27
DGE-25	HGR-16									
DGEA-18	HGW-16									
DGP...-32							196 789	HMVA-DL32		
DGP...-40		40	22	18	85	80	196 790	HMVA-DLA40		
DGE-40										
DGP...-25	HGP-16	40	22	14	85	80	196 788	HMVA-DLA18/25	177 768	HMSV-28
DGE-25	HGR-25									
DGEA-18	HGW-25									
DGP...-32							196 789	HMVA-DL32		
DGP...-40		40	22	18	85	80	196 790	HMVA-DLA40		
DGE-40										
DGP...-32	HGP-25	50	24	18	100	100	196 789	HMVA-DL32	177 769	HMSV-29
DGP...-40	HGR-32						196 790	HMVA-DLA40		
DGE-40	HGW-32									
DGP...-40	HGP-35	60	28	18	110	100	196 790	HMVA-DLA40	177 770	HMSV-30
DGE-40	HGR-40									
	HGW-40									

System components
Adapters

3.2


DG.../HGDS combination

Technical data

FESTO

Adapter kit HMVA, HMSV

Material:
Wrought aluminium alloy, anodised
Centring sleeves: High-alloy steel
Free of copper, PTFE and silicone




Dovetail mounting

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Dovetail mounting



- 1 Linear drive
- 2 Swivel/gripper unit
- 3 Adapter kit HMSV
- 4 Adapter kit HMSV
- 5 Adapter kit HMVA

Drive	Gripper	H2	Part No.	Type	Part No.	Type
DGP...-25	HGDS-12 ... 20		196 788	HMVA-DLA18/25	177 653	HMSV-7
DGE-25		14			534 290	HMSV-38
DGEA-18						
DGP...-32	HGDS-12 ... 20	18	196 789	HMVA-DL32		
DGP...-40	HGDS-12 ... 20	18	196 790	HMVA-DLA40		
DGE-40						

DRQD/HGPT combination

Technical data

FESTO

System components
Adapters

3.2


Adapter kit HAPG

Material:

Wrought aluminium alloy, anodised

Centring pins/sleeves: High-alloy steel

Free of copper, PTFE and silicone




Direct mounting
DRQD-...-FW with flanged shaft

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting via flanged shaft and air throughfeed



- 1 Drive
- 2 Gripper

Drive	Gripper	B1	D1	D2	H1	L1	Part No.	Type
Flanged shaft with air throughfeed SD...								
DRQD-12	HGPT-16	11	M2	M3	35.5	34	537 171	HAPG-SD2-22
DRQD-16				M4				
DRQD-12	HGPT-20	11	M3	M3	44	34	537 177	HAPG-SD2-24
DRQD-16				M4				
DRQD-16/-20	HGPT-25	11	M4	M4	36	52	537 181	HAPG-SD2-25
DRQD-20	HGPT-35	12	M4	M4	42	64	537 173	HAPG-SD2-23
DRQD-25				M6				
DRQD-25/-32	HGPT-40	15	M5	M6	50	80	537 184	HAPG-SD2-26
DRQD-32	HGPT-50	15	M6	M8	85.5	100	537 186	HAPG-SD2-27
DRQD-40				M6				
DRQD-40/-50	HGPT-63	15	M6	M8	83	125	537 188	HAPG-SD2-28
Flanged shaft with air throughfeed E...								
DRQD-16	HGPT-16	8	M2.5	M4	35	44	544 641	HAPG-SD2-47
	HGPT-20		M3					
DRQD-16	HGPT-25	9	M4	M4	42	64	544 642	HAPG-SD2-48
DRQD-20	HGPT-25/-35	9	M4	M4	42	64	544 642	HAPG-SD2-48
DRQD-25	HGPT-35	12	M4	M4	42	64	537 173	HAPG-SD2-23
DRQD-25/-32	HGPT-40	15	M5	M6	50	80	537 184	HAPG-SD2-26
DRQD-32	HGPT-50	11	M6	M6	60	100	544 643	HAPG-SD2-49

DRQD/HGPL combination

Technical data

FESTO


Adapter kit HAPG

Material:

Wrought aluminium alloy, anodised

Centring sleeves: High-alloy steel

Free of copper, PTFE and silicone




Direct mounting

DRQD-...-FW with flanged shaft

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting via flanged shaft and air throughfeed



-  - Note

Only in combination with semi-rotary drive DRQD-...-YSRJ (with adjustable shock absorbers).

1 Drive
2 Gripper

Drive	Gripper	B1	D1	D2	H1	L1	Part No.	Type
Flanged shaft with air throughfeed SD...								
DRQD-16	HGPL-14	12	M4	M4	35	75	537 310	HAPG-SD2-31
DRQD-20								
DRQD-25	HGPL-25	14	M5	M6	60	75	537 311	HAPG-SD2-29
DRQD-32								
DRQD-40	HGPL-40	20	M8	M8	60	120	537 312	HAPG-SD2-30
DRQD-50								
Flanged shaft with air throughfeed E...								
DRQD-16	HGPL-14	9	M4	M4	35	75	544 644	HAPG-SD2-45
DRQD-20								
DRQD-25	HGPL-25	11	M5	M6	60	75	544 645	HAPG-SD2-46
DRQD-32								

DRQD/HGPP combination

Technical data

FESTO


Adapter kit HAPG

Material:


Wrought aluminium alloy, anodised

Centring pins/sleeves: High-alloy steel

Free of copper, PTFE and silicone



Direct mounting
DRQD-...-FW with flanged shaft



Direct mounting
DRQD-...-ZW with spigot shaft


System components
Adapters

3.2

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting via flanged shaft and air throughfeed SD.../E...



- 1 Drive
- 2 Gripper

Drive	Gripper	B1	B2	D1	D2	D4 Ø	H1	Part No.	Type
DRQD-16-FW DRQD-20-FW	HGPP-12	11.8	9	M3	M4	56	36	191 255	HAPG-SD2-14
DRQD-20-FW DRQD-25-FW	HGPP-16	11.8	9	M3	M4 M6	80	40	191 256	HAPG-SD2-15
DRQD-25-FW DRQD-32-FW	HGPP-20	11.8	9	M4	M6	90	46	191 257	HAPG-SD2-16
DRQD-16-FW DRQD-20-FW	HGPP-10	11.8	9	M3	M4	43	31	526 023	HAPG-SD2-17
DRQD-32-FW DRQD-40-FW DRQD-50-FW	HGPP-25	17.8	15	M5	M6 M8	120	53	526 024	HAPG-SD2-18
DRQD-40-FW DRQD-50-FW	HGPP-32	18.8	15	M5	M8	153	60	526 025	HAPG-SD2-19

DRQD/HGPP combination


Technical data

FESTO

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting via spigot shaft



1 Drive
2 Gripper

Drive	Gripper	B1	B2	D1	D2	D3 Ø	H1	L1	Part No.	Type
DRQD-16-ZW	HGPP-12	33	26	M3	M4	34	38	38	191 258	HAPG-40
DRQD-20-ZW	HGPP-12	41	34	M3	M5	38	38	38	191 259	HAPG-41
DRQD-25-ZW	HGPP-16	49	42	M3	M5	42	42	50	191 260	HAPG-42
DRQD-32-ZW	HGPP-20	52	42	M4	M5	45	48	48	191 261	HAPG-43

DRQD/HGP, HGD, HGW, HGR combination

Technical data

FESTO


Adapter kit DRQD-...-AS, HAPG

Material:


Wrought aluminium alloy, anodised

Centring pins/sleeves: High-alloy steel

Free of copper, PTFE and silicone



Direct mounting
DRQD-...-FW with flanged shaft



Direct mounting
DRQD-...-ZW with spigot shaft

System components
Adapters


3.2

Dimensions and ordering data


Download CAD data → www.festo.com/en/engineering

Direct mounting via flanged shaft and air throughfeed SD...

DRQD-...-AS1/-AS2



HAPG-34/-35



Drive	Gripper	B1	B2	D1	D2	D3	D4	E1	L1	≡C1	≡C2	≡C3	Part No.	Type
Flanged shaft														
DRQD-6-...-FW	HGP-6	10	–	M3	M3	M4	28	–	–	2.5	2.5	2	187 568	HAPG-34
DRQD-8-...-FW	HGR-10													
DRQD-12-...-FW	HGW-10													
DRQD-8-...-FW	HGD-16	8	–	M3	M3	M4	29	–	–	2.5	2.5	2	187 569	HAPG-35
DRQD-12-...-FW														
Flanged shaft and air throughfeed SD...														
DRQD-8	HGP-6	10.2	8	M3	M2	M4	28	–	–	2.5	2	–	187 432	DRQD-8-...-AS1 ¹⁾
DRQD-12	HGR-10 HGW-10												187 433	DRQD-12-...-AS1 ¹⁾
DRQD-8	HGD-16	10.2	8	M3	M2	M4	29	–	–	2.5	2	–	187 432	DRQD-8-...-AS2 ¹⁾
DRQD-12													187 433	DRQD-12-...-AS2 ¹⁾

1) Semi-rotary drives DRQD are ordered using the product modules with the corresponding adapter kit (code AS).

DRQD/HGP, HGD, HGW, HGR combination

Technical data


FESTO

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering


Direct mounting via flanged shaft with air throughfeed SD...

HAPG-SD2-5/-8/-11/-13/-20



- 1 Drive
- 2 Gripper

HAPG-SD2-1/-2/-3/-4/-6/-7/-9/-10/-12/-21



- 1 Drive
- 2 Gripper

Drive	Gripper	B1	B2	D1	D2	D3	D4	E1	L1	⌀C1	⌀C2	⌀C3	Part No.	Type
DRQD-16-...-FW	HGP-6 HGR-10 HGW-10	9	–	M4	M3	34	–	M3	–	3	2.5	2	187 566	HAPG-SD2-12
DRQD-16-...-FW	HGD-16	9	–	M3	M4	34	–	M3	–	2.5	3	2	187 567	HAPG-SD2-13
DRQD-16-...-FW	HGP-10 HGR-16 HGW-16	9	–	M4	M3	37	–	M3	35	3	2.5	2	184 477	HAPG-SD2-1
DRQD-16-...-FW	HGP-16	9	–	M4	M4	42	–	M3	35	3	3	2	184 478	HAPG-SD2-2
	HGR-25 HGW-25							M5						
DRQD-20-...-FW	HGP-16	9	–	M4	M4	42	–	M3	38	3	3	2	184 479	HAPG-SD2-3
	HGP-20 HGR-25 HGW-25							M5						
DRQD-20-...-FW	HGP-25 HGR-32 HGW-32	9	–	M4	M6	44	–	G1/8	38	3	5	2	184 480	HAPG-SD2-4
DRQD-20-...-FW	HGD-32	9	–	M3	M4	45	–	M5	–	2.5	3	2	184 481	HAPG-SD2-5
DRQD-25-...-FW	HGP-16	9	–	M6	M4	50	–	M3	47	5	3	2	184 482	HAPG-SD2-6
	HGP-20 HGR-25 HGW-25							M5						
DRQD-25-...-FW	HGP-25 HGR-32 HGW-32	9	–	M6	M6	50	–	G1/8	47	5	5	2	184 483	HAPG-SD2-7
DRQD-25-...-FW	HGD-50	9	–	M5	M6	70	–	G1/8	–	4	5	2	184 484	HAPG-SD2-8
DRQD-32-...-FW	HGP-25 HGR-32 HGW-32	9	–	M6	M6	60	–	G1/8	58	5	5	2	184 485	HAPG-SD2-9
DRQD-32-...-FW	HGP-35 HGR-40 HGW-40	9	–	M6	M8	60	–	G1/8	58	5	6	2	184 486	HAPG-SD2-10
DRQD-32-...-FW	HGD-50	9	–	M5	M6	70	–	G1/8	–	4	5	2	184 487	HAPG-SD2-11
DRQD-40-...-FW DRQD-50-...-FW	HGD-50	15	–	M5	M8	90	–	G1/8	–	6	6	2	526 026	HAPG-SD2-20
DRQD-40-...-FW DRQD-50-...-FW	HGP-35 HGR-40 HGW-40	12	–	M8	M8	80	–	G1/8	–	6	6	2	526 027	HAPG-SD2-21

DRQD/HGP, HGD, HGW, HGR combination

Technical data


FESTO

Dimensions and ordering data


Download CAD data → www.festo.com/en/engineering

Direct mounting via spigot shaft

HAPG-23/-24



HAPG-18/-19/-20/-21/-22



Drive	Gripper	B1	D1	D2	D3	L1	L2	≅ 1	≅ 2	Part No.	Type
DRQD-16-...-ZW	HGP-10 HGR-16 HGW-16	28	M3	M4	33	—	—	2.5	3	163 267	HAPG-18
DRQD-16-...-ZW	HGP-16/-20 HGR-25 HGW-25	28	M4	M4	34	—	—	3	3	163 268	HAPG-19
DRQD-20-...-ZW	HGP-16/-20 HGR-25 HGW-25	38	M4	M5	41	—	—	3	4	163 269	HAPG-20
DRQD-20-...-ZW	HGP-25 HGR-32 HGW-32	38	M6	M5	41	—	—	5	4	163 270	HAPG-21
DRQD-20-...-ZW	HGD-32	29	M3	M5	45	32	10	2.5	4	163 272	HAPG-23
DRQD-25-...-ZW	HGP-25 HGR-32 HGW-32	46	M6	M5	41	—	—	5	4	163 271	HAPG-22
DRQD-25-...-ZW	HGD-50	29	M5	M5	70	42	12	4	4	163 273	HAPG-24

System components
Adapters

3.2

DRQD/HGPC combination

Technical data




Adapter kit HAPG

Material:

Wrought aluminium alloy, anodised

Centring sleeves: High-alloy steel

Free of copper, PTFE and silicone




Direct mounting

DRQD-...-FW with flanged shaft

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting via flanged shaft and air throughfeed



- 1 Drive
- 2 Gripper

Drive	Gripper	B1	D1	D2	D3	H1	L1	Part No.	Type
Flanged shaft with air throughfeed SD...									
DRQD-12	HGPC-12	10	M4	M4	M4	32.6	42	542 671	HAPG-SD2-41
DRQD-16									
DRQD-16	HGPC-16	10	M5	M4	M4	39	51	542 668	HAPG-SD2-42
DRQD-20									
DRQD-20	HGPC-20	9	M6	M4	M4	50	65	542 669	HAPG-SD2-43
DRQD-25	HGPC-20	9	M6	M6	M4	50	65	542 758	HAPG-SD2-44

DRQD/HGPM, HGWM combination

Technical data


FESTO

Adapter kit DRQD-...-A...-HS

Material:

Zinc-coated steel

Free of copper, PTFE and silicone




Direct mounting
via hollow bolt

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting via hollow bolt



Drive	Gripper	B1	B2	B3	D1	D2	±1	Part No.	Type
DRQD-6	HGPM-08-...-G8	15.2	13	9.6	M3	16	1.5	187 431	DRQD-6-...-A08-HS ¹⁾
DRQD-8	HGWM-08-...-G8							187 432	DRQD-8-...-A08-HS ¹⁾
DRQD-12	HGWM-08-...-G8							187 433	DRQD-12-...-A08-HS ¹⁾
DRQD-6	HGPM-12-...-G8	20.2	18	14.6	M3	21	1.5	187 431	DRQD-6-...-A12-HS ¹⁾
DRQD-8	HGWM-12-...-G8							187 432	DRQD-8-...-A12-HS ¹⁾
DRQD-12	HGWM-12-...-G8							187 433	DRQD-12-...-A12-HS ¹⁾

1) Semi-rotary drives DRQD are ordered using the product modules with the corresponding adapter kit (code A...) and hollow bolt (code HS)

DRQD/HGDT combination

Technical data

FESTO


Adapter kit HAPG

Material:

Wrought aluminium alloy, anodised

Centring pins/sleeves: High-alloy steel

Free of copper, PTFE and silicone




Direct mounting
DRQD-...-FW with flanged shaft

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting via flanged shaft and air throughfeed



1 Drive
2 Gripper

Drive	Gripper	B1	D1	D2	L1	Part No.	Type
Flanged shaft with air throughfeed SD... and E...							
DRQD-16	HGDT-25	49	M3	M4	10	542 439	HAPG-SD2-32
DRQD-20	HGDT-25	49	M3	M4	10	542 440	HAPG-SD2-33
DRQD-25				M6			
DRQD-20	HGDT-35	58	M3	M4	10	542 441	HAPG-SD2-34
DRQD-25				M6			
DRQD-32				M6			
DRQD-25	HGDT-40	74	M5	M6	10	542 442	HAPG-SD2-35
DRQD-32							
DRQD-32	HGDT-50	92	M6	M5	11.5	542 443	HAPG-SD2-36

DSL, DSM/HGPP combination

Technical data

FESTO


Adapter kit HAPG

Material:


Wrought aluminium alloy, anodised

Centring pins/sleeves: High-alloy steel

Free of copper, PTFE and silicone



Direct mounting
DSL-...-KF with spigot shaft




Direct mounting
DSM with spigot shaft

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting via spigot shaft



Drive	Gripper	B1	B2	D1	D2	D3 Ø	H1	L1	Part No.	Type
DSL-20-KF DSM-16	HGPP-12	33	26	M3	M4	3	38	38	191 258	HAPG-40
DSL-25-KF DSM-25	HGPP-12	41	34	M3	M5	38	38	38	191 259	HAPG-41
DSL-32-KF DSM-32	HGPP-16	49	42	M3	M5	42	42	50	191 260	HAPG-42
DSL-40-KF DSM-40	HGPP-20	52	42	M4	M5	45	48	48	191 261	HAPG-43

DSL, DSM/HGP, HGD, HGW, HGR combination

FESTO

Technical data


Adapter kit HAPG

Material:


Wrought aluminium alloy, anodised

Centring sleeves: High-alloy steel

Free of copper, PTFE and silicone



Direct mounting
DSL with spigot shaft



Direct mounting
DSM with spigot shaft

System components
Adapters


3.2

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

Direct mounting via flanged shaft

HAPG-34/-35 for parallel gripper HGP, three-point gripper HGD, radial gripper HGR, angle gripper HGW



1 Drive
2 Gripper

Drive	Gripper	B1	D1	D2	D3	D4	L1	L2	≙ 1	≙ 2	≙ 3	Part No.	Type
DSM-6/-8/-10	HGP-6 HGR-10 HGW-10	10	M3	M3	M4	28	–	–	2.5	2.5	2	187 568	HAPG-34
DSM-8/-10	HGD-16	8	M3	M3	M4	29	–	–	2.5	2.5	2	187 569	HAPG-35

DSL, DSM/HGD, HGP, HGW, HGR combination

Technical data


FESTO

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering


Direct mounting via spigot shaft

HAPG-17 ... 22 for parallel gripper HGP, radial gripper HGR, angle gripper HGW



Direct mounting via spigot shaft

HAPG-23/-24 for three-point gripper HGD



Drive	Gripper	B1	D1	D2	D3	D4	L1	L2	≈C 1	≈C 2	≈C 3	Part No.	Type
DSM-12 DSL-16	HGP-10 HGR-16 HGW-16	27	M3	M3	24	–	–	–	2.5	2.5	–	163 266	HAPG-17
DSM-16 DSL-20	HGP-10 HGR-16 HGW-16	28	M3	M4	33	–	–	–	2.5	3	–	163 267	HAPG-18
DSM-16 DSL-20	HGP-16 HGP-20 HGR-25 HGW-25	28	M4	M4	34	–	–	–	3	3	–	163 268	HAPG-19
DSM-25 DSL-25	HGP-16 HGP-20 HGR-25 HGW-25	38	M4	M5	41	–	–	–	3	4	–	163 269	HAPG-20
DSM-25 DSL-25	HGP-25 HGR-32 HGW-32	38	M6	M5	41	–	–	–	5	4	–	163 270	HAPG-21
DSM-32 DSL-32	HGP-25 HGR-32 HGW-32	46	M6	M5	41	–	–	–	5	4	–	163 271	HAPG-22
DSM-25 DSL-25	HGD-32	29	M3	M5	45	–	32	10	2.5	4	–	163 272	HAPG-23
DSM-32 DSL-32	HGD-50	29	M5	M5	70	–	42	12	4	4	–	163 273	HAPG-24

DPZ/HGP, HGW, HGR combination

Technical data

FESTO

System components
Adapters

3.2


Adapter kit HAPG

Material:

Wrought aluminium alloy, anodised

Centring pins/sleeves: High-alloy steel


Free of copper, PTFE and silicone



Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

HAPG-1/-2



- 1 Drive
- 2 Gripper

Drive	Gripper	B1	D1	D2	H1	L1	L2	Part No.	Type
DPZ-10	HGP-10	10	M3	M5	36	22.6	18	163 250	HAPG-1
DPZ-16	HGR-16								
DPZJ-10	HGW-16								
DPZJ-16									
DPZ-16	HGP-16	10	M4	M5	36	34.6	18	163 251	HAPG-2
DPZJ-16	HGP-20								
	HGR-25								
	HGW-25								

DPZ/HGP, HGW, HGR combination


Technical data

FESTO

Dimensions and ordering data

Download CAD data → www.festo.com/en/engineering

HAPG-3/-4



Drive	Gripper	B1	D1	D2	H1	L1	L2	Part No.	Type
DPZ-20 DPZJ-20	HGP-16 HGP-20 HGR-25 HGW-25	12	M4	M6	37	34.6	19	163 252	HAPG-3
DPZ-25 DPZ-32 DPZJ-25 DPZJ-32	HGP-25 HGR-32 HGW-32	12	M6	M6	49	41.5	27.5	163 253	HAPG-4