

Metal braided shielded hose PX-6

Part number: 4094

FESTO

Type to be discontinued. Available until 2011.



Data sheet

| Feature | Value |
|--|--------------------------|
| Outside diameter | 9 mm |
| Bending radius relevant for flow rate | 30 mm |
| Inside diameter | 6 mm |
| Temperature dependent working pressure | 0 ... 12 bar |
| Ambient temperature | -20 ... 80 °C |
| Product weight according to length | 0.14 kg/m |
| Color | silver |
| Shore hardness | 75 +/- 5 |
| Materials note | Contains PWIS substances |
| Materials information for tubing | NBR |