


Quick coupling socket KDS6-N-9

Part number: 531655
Product to be discontinued

FESTO

Self-closing, for safety coupling per ISO 4414
Type to be discontinued. Available until 2018. See Support Portal for alternative products.



Data sheet

Feature	Value
Nominal size	7 mm
Operating pressure complete temperature range	-0.5 ... 12 bar
Standard nominal flow rate	1,121 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	-10 ... 60 °C
Authorization	BIA TÜV
Product weight	97 g
Pneumatic connection, port 1	N-9
Materials note	Conforms to RoHS