Parallel kit EAMM-U-60-D40-55A-91

Part number: 1210438

Data sheet

Feature	Value
Size	60
Mounting position	optional
Gear unit ratio	1:1
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	26.7 kgmm²
Frictional torque independent of load	0.07 Nm
Transmittable torque	3 Nm
Product weight	1040 g
Interface code, actuator	D40B
Interface code, motor in	55A
Note on materials	RoHS-compliant