Coupling EAMC-30-32-6-14

Part number: 1233256

Data sheet

Feature	Value
Mounting diameter 1	6 mm
Mounting diameter 2	14 mm
Size	30
Nominal length	32 mm
Mounting position	optional
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	5.87 kgmm²
Transmittable torque	6.5 Nm
Product weight	48 g
Note on materials	RoHS-compliant