Axial kit EAMM-A-R27-40G

Part number: 1456622

Data sheet

Feature	Value
Mounting position	optional
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Transmittable torque	2 Nm
Product weight	240 g
Interface code, actuator	R27
Interface code, motor in	40G
Note on materials	RoHS-compliant