Coupling housing EAMK-A-D19-28D

Part number: 1087585



Data sheet

Feature	Value
Mounting position	Any
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 °C...60 °C
Product weight	51 g
Interface code, actuator	D19A
Interface code, coupling housing	28D
Note on materials	RoHS-compliant