# Quick coupling EAMC-30-32-6-14

Part number: 1233256

## Data sheet

| Feature | Value |
|---|---|
| Diameter of holder 1 | 6 mm |
| Diameter of holder 2 | 14 mm |
| Size | 30 |
| Nominal length | 32 mm |
| Mounting position | Any |
| Max. rotational speed | 8000 1/min |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C...60 °C |
| Relative air humidity | 0 - 95 % |
| Ambient temperature | -25 °C...60 °C |
| Mass moment of inertia | 5.87 kgmm² |
| Transferable torque | 6.5 Nm |
| Product weight | 48 g |
| Note on materials | RoHS-compliant |