# Blanking plug QSC-6H-100

Part number: 130700

## Data sheet

| Feature | Value |
|---|---|
| Size | Standard |
| Mounting position | Any |
| Design | Blanking plug |
| Pack size | 100 |
| Operating pressure for entire temperature range | -0.095 MPa...0.6 MPa<br>-0.95 bar...6 bar<br>-13.775 psi...87 psi |
| Temperature-dependent operating pressure | -0.095 MPa...1.4 MPa<br>-0.95 bar...14 bar<br>-13.775 psi...203 psi |
| Maritime classification | See certificate |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-]<br>Water as per manufacturer's declaration at www.festo.com |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Cleanroom class | Statically installed element, no meaningful evaluation possible according to ISO 14644-1 |
| Ambient temperature | -10 °C...80 °C |
| Product weight | 0.5 g |
| Pneumatic connection 1 | Push-in sleeve Ø 6 mm |
| Note on materials | RoHS-compliant |
| Housing material | PBT |