

# Spojni vod

## NEBC-H25G8-ES-5-N-B-LE4

Broj artikla: 8132476

Komponenta koja će prestati da se proizvodi

Komponenta se više ne proizvodi. Isporučuje se do 2025. Vidi Support Portal za alternativni proizvod.

FESTO



## Tehnički podaci

Svojstvo	Vrednost
Cable identification	Without inscription label holder
Težina proizvoda	160 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	okruglo
Electrical connection 1, connection type	Utičnica
Electrical connection 1, cable outlet	Ravno
Electrical connection 1, connection technology	HR25
Electrical connection 1, number of pins/wires	8
Electrical connection 1, occupied pins/wires	4
Electrical connection 1, type of mounting	Screw lock
Electrical connection 2, function	Controller side
Electrical connection 2, connection type	Kabl
Electrical connection 2, connection technology	otvoreni kraj
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
Područje pogonskog napona DC	0 ... 42 V
Područje pogonskog napona AC	0 ... 30 V
Strujna opteretivost kod 40°C	1 A
Čvrstoća na udarno naprezanje	3 kV
Shielding	Da
Dužina kabla	4,93 m
Svojstvo kabla	prikladno za energetski lanac
Uslovi ispitivanja kabla	Uslovi ispitivanja na zahtev
Bending radius, fixed cable installation	≥ 18,4 mm
Bending radius, flexible cable installation	≥ 34,5 mm
Prečnik kabla	4,6 mm
Struktura kabla	4x0,14
Nazivni presek provodnika	0,14 mm <sup>2</sup>
Krajevi žica	Cut off bluntly
Mehanička zaštita	Zavisno od priključnog bloka
Note on degree of protection	Zavisno od priključnog bloka
Temperatura okoline	-10 ... 60 °C
Temperatura okoline kod pokretnog postepenja kablova	-5 ... 60 °C
Temperatura ležaja	-10 ... 60 °C
CE znak (vidi izjavu o usklađenosti)	prema EU-EMV-smernici in accordance with EU RoHS directive
PWIS conformity	VDMA24364 zone III
Materijal - napomena	RoHS komfornost
Stepen zagađenja	1
Klasa korozione otpornosti KBK	0 - No corrosion stress
Material cable sheath	PVC
Boja izolacije	sivo
Material housing	Mesing niklovan
Boja kućišta	srebrno
Material insulation	PPS