

Tee Push-in Fittings, Type QBT


Inch Series

Tee Fittings

UNF Thread

Inch Tubing Connection

Sold in 20 piece packages



Dimensions and Ordering Data


Type	Thread Connection D	Orifice Ø inches	For Inch tubing O.D. D1	Weight oz	Dimensions inches						
					a	b	c	e	f	g	≡
UNF Thread with Sealing Ring											
QBT-10/32UNF-1/8-U	UNF10-32	0.100	1/8	0.15	0.142	0.303	0.433	1.005	0.429	0.571	5/16
QBT-10/32UNF-5/32-U		0.100	5/32	0.30	0.142	0.413	0.638	1.469	0.701	0.843	3/8
QBT-10/32UNF-3/16-U		0.120	3/16	0.33	0.142	0.453	0.661	1.504	0.780	0.921	7/16
QBT-10/32UNF-1/4-U		0.100	1/4	0.50	0.142	0.512	0.681	1.606	0.878	1.020	1/2

Tee Fittings

NPT Thread

Inch Tubing Connection

Sold in 10 piece packages



Dimensions and Ordering Data

Type	Thread Connection D	Orifice Ø inches	For Inch tubing O.D. D1	Weight oz	Dimensions inches						
					a	b	c	e	f	g	≡
NPT Threads											
QBT-1/8-1/8-U	NPT1/8	0.100	1/8	0.31	0.335	0.303	0.433	1.055	0.602	0.760	7/16
QBT-1/8-5/32-U		0.120	5/32	0.38	0.335	0.413	0.638	1.469	0.827	0.984	7/16
QBT-1/8-3/16-U		0.120	3/16	0.41	0.335	0.453	0.661	1.504	0.827	0.984	7/16
QBT-1/8-1/4-U		0.177	1/4	0.59	0.335	0.512	0.681	1.606	0.937	1.095	1/2
QBT-1/8-5/16-U		0.236	5/16	0.69	0.335	0.571	0.716	1.756	1.000	1.158	9/16
QBT-1/4-3/16-U	NPT1/4	0.120	3/16	0.64	0.413	0.453	0.661	1.504	0.905	1.102	9/16
QBT-1/4-1/4-U		0.177	1/4	0.70	0.413	0.512	0.681	1.606	1.004	1.201	9/16
QBT-1/4-5/16-U		0.236	5/16	0.78	0.413	0.571	0.716	1.756	1.039	1.236	9/16
QBT-1/4-3/8-U		0.315	3/8	1.08	0.413	0.689	0.783	1.878	1.063	1.260	11/16
QBT-3/8-1/4-U	NPT3/8	0.177	1/4	1.03	0.453	0.512	0.681	1.606	1.024	1.240	11/16
QBT-3/8-5/16-U		0.236	5/16	1.09	0.453	0.571	0.716	1.756	1.059	1.276	11/16
QBT-3/8-3/8-U		0.315	3/8	1.23	0.453	0.689	0.783	1.878	1.083	1.299	11/16
QBT-3/8-1/2-U		0.394	1/2	1.59	0.453	0.827	0.905	2.245	1.220	1.437	3/4
QBT-1/2-3/8-U	NPT1/2	0.315	3/8	1.94	0.571	0.689	0.783	1.878	1.142	1.417	7/8
QBT-1/2-1/2-U		0.394	1/2	2.06	0.571	0.827	0.905	2.245	1.280	1.555	7/8