

Filter cartridges

FESTO



Filter cartridges

Accessories

FESTO

Filter cartridges, D series,
metal design



Ordering data				
Size	Filter cartridge	Grade of filtration [µm]	Part No.	Type
Micro	Filter cartridge	5	526818	LFP-D-MICRO-5M
Mini	Micro-filter cartridge	0.01	162674	MS4/D-MINI-LFM-A
	Fine-filter cartridge	1	162677	MS4/D-MINI-LFM-B
	Filter cartridge (colour: blue)	5	159640	LFP-D-MINI-5M
	Filter cartridge (colour: white)	40	363665	LFP-D-MINI-40M
	Activated carbon filter cartridge	–	532912	MS4/D-MINI-LFX
Midi	Micro-filter cartridge	0.01	162675	LFMAP-D-MIDI
	Fine-filter cartridge	1	162678	LFMBP-D-MIDI
	Filter cartridge (colour: blue)	5	159594	LFP-D-MIDI-5M
	Filter cartridge (colour: white)	40	363667	LFP-D-MIDI-40M
	Activated carbon filter cartridge	–	532788	LFACP-MIDI
Maxi	Micro-filter cartridge	0.01	162676	LFMAP-D-MAXI
	Fine-filter cartridge	1	162679	LFMBP-D-MAXI
	Filter cartridge (colour: blue)	5	159641	LFP-D-MAXI-5M
	Filter cartridge (colour: white)	40	363664	LFP-D-MAXI-40M
	Activated carbon filter cartridge	–	532789	LFACP-MAXI

Filter cartridges

Accessories



Filter cartridges, D series,
polymer design



Ordering data				
Size	Filter cartridge	Grade of filtration [μm]	Part No.	Type
Mini	Filter cartridge	5	547957	LFP-DB-MINI-5M
	Filter cartridge	40	534502	MS4-LFP-E

Filter cartridges

Accessories

FESTO

Filter cartridges, MS4/MS6 series



Ordering data				
Size	Filter cartridge	Grade of filtration [µm]	Part No.	Type
MS4	Micro-filter cartridge	0.01	162674	MS4/D-MINI-LFM-A
	Fine-filter cartridge	1	162677	MS4/D-MINI-LFM-B
	Filter cartridge (colour: blue)	5	534501	MS4-LFP-C
	Filter cartridge (colour: white)	40	534502	MS4-LFP-E
	Activated carbon filter cartridge	–	532912	MS4/D-MINI-LFX
MS6	Micro-filter cartridge	0.01	532909	MS6-LFM-A
	Fine-filter cartridge	1	532910	MS6-LFM-B
	Filter cartridge (colour: blue)	5	534499	MS6-LFP-C
	Filter cartridge (colour: white)	40	534500	MS6-LFP-E
	Activated carbon filter cartridge	–	532911	MS6-LFX
High flow rate HF				
MS6	Micro-filter cartridge	0.01	552093	MS6-LFM-A-HF
	Fine-filter cartridge	1	552092	MS6-LFM-B-HF
	Activated carbon filter cartridge	–	552094	MS6-LFX-HF
Range of application HP, suitable for sealing air and cleaning air				
MS6	Micro-filter cartridge	0.01	547922	MS6-LFM-AI:T 
	Fine-filter cartridge	1	547923	MS6-LFM-BI:T 
	Activated carbon filter cartridge	–	547925	MS6-LFX-AKI:T 

Filter cartridges

Accessories

Filter cartridges, MS9 series



Ordering data				
Size	Filter cartridge	Grade of filtration [μm]	Part No.	Type
MS9	Micro-filter cartridge	0.01	553036	MS9-LFM-A
	Fine-filter cartridge	1	553037	MS9-LFM-B
	Filter cartridge	5	570309	MS9-LFP-C
	Filter cartridge	40	570310	MS9-LFP-E
	Activated carbon filter cartridge	–	552946	MS9-LFX
High flow rate HF				
MS9	Micro-filter cartridge	0.01	552944	MS9-LFM-A-HF
	Fine-filter cartridge	1	552945	MS9-LFM-B-HF

Filter cartridges

Accessories

FESTO


Filter cartridges, MS12 series



MS12-LFM-B



MS12-LFM-A



MS12-LFX

Ordering data				
Size	Filter cartridge	Grade of filtration [μm]	Part No.	Type
MS12	Micro-filter cartridge	0.01	537146	MS12-LFM-A
	Fine-filter cartridge	1	537145	MS12-LFM-B
	Filter cartridge	5	537143	MS12-LFP-C
	Filter cartridge	40	537144	MS12-LFP-E
	Activated carbon filter cartridge	–	537147	MS12-LFX

- 2 - Type to be discontinued
Available up to December 2014


FESTO

Filter cartridges

Accessories

Filter cartridges, H series

- For fine and micro filters, H series
- For adsorption dryer LDF



Ordering data								
Filter cartridge	Grade of filtration [µm]	For adsorption dryer LDF	Connection	D1 Ø	D2 Ø	L1	Part No.	Type
Micro-filter cartridge	0.01	Inlet filter (LDF-H1-...-H3)	G1/4	35	6.75	74	185688	LFMAP-1/4-H
		Inlet filter (LDF-H4-...-H7)	G1/2	48	21.7	126	162824	LFMAP-1/2-H
		–	G3/4	72	33	168.8	162825	LFMAP-3/4-H
		–	G1	72	33	268.8	162826	LFMAP-1-H
Fine-filter cartridge	1	Outlet filter (LDF-H1-...-H3)	G1/4	35	6.75	74	185689	LFMBP-1/4-H
		Outlet filter (LDF-H4-...-H7)	G1/2	48	21.7	126	162827	LFMBP-1/2-H
		–	G3/4	72	33	168.8	162828	LFMBP-3/4-H
		–	G1	72	33	268.8	162829	LFMBP-1-H