

# Filter cartridges



# Filter cartridges

Accessories

**FESTO**

Filter cartridges, D series,  
metal design



Ordering data				
Size	Filter cartridge	Grade of filtration [µm]	Part No.	Type
Micro	Filter cartridge	5	526818	LFP-D-MICRO-5M
Mini	Micro-filter cartridge	0.01	162674	MS4/D-MINI-LFM-A
	Fine-filter cartridge	1	162677	MS4/D-MINI-LFM-B
	Filter cartridge (colour: blue)	5	159640	LFP-D-MINI-5M
	Filter cartridge (colour: white)	40	363665	LFP-D-MINI-40M
	Activated carbon filter cartridge	–	532912	MS4/D-MINI-LFX
Midi	Micro-filter cartridge	0.01	162675	LFMAP-D-MIDI
	Fine-filter cartridge	1	162678	LFMBP-D-MIDI
	Filter cartridge (colour: blue)	5	159594	LFP-D-MIDI-5M
	Filter cartridge (colour: white)	40	363667	LFP-D-MIDI-40M
	Activated carbon filter cartridge	–	532788	LFACP-MIDI
Maxi	Micro-filter cartridge	0.01	162676	LFMAP-D-MAXI
	Fine-filter cartridge	1	162679	LFMBP-D-MAXI
	Filter cartridge (colour: blue)	5	159641	LFP-D-MAXI-5M
	Filter cartridge (colour: white)	40	363664	LFP-D-MAXI-40M
	Activated carbon filter cartridge	–	532789	LFACP-MAXI

# Filter cartridges

Accessories

Filter cartridges, D series,  
polymer design



Ordering data				
Size	Filter cartridge	Grade of filtration [ $\mu\text{m}$ ]	Part No.	Type
Mini	Filter cartridge	5	<b>547957</b>	<b>LFP-DB-MINI-5M</b>
	Filter cartridge	40	<b>534502</b>	<b>MS4-LFP-E</b>




## Filter cartridges

Accessories

**FESTO**

Filter cartridges, MS4/MS6 series



Ordering data				
Size	Filter cartridge	Grade of filtration [µm]	Part No.	Type
MS4	Micro-filter cartridge	0.01	<b>162674</b>	<b>MS4/D-MINI-LFM-A</b>
	Fine-filter cartridge	1	<b>162677</b>	<b>MS4/D-MINI-LFM-B</b>
	Filter cartridge (colour: blue)	5	<b>534501</b>	<b>MS4-LFP-C</b>
	Filter cartridge (colour: white)	40	<b>534502</b>	<b>MS4-LFP-E</b>
	Activated carbon filter cartridge	–	<b>532912</b>	<b>MS4/D-MINI-LFX</b>
MS6	Micro-filter cartridge	0.01	<b>532909</b>	<b>MS6-LFM-A</b>
	Fine-filter cartridge	1	<b>532910</b>	<b>MS6-LFM-B</b>
	Filter cartridge (colour: blue)	5	<b>534499</b>	<b>MS6-LFP-C</b>
	Filter cartridge (colour: white)	40	<b>534500</b>	<b>MS6-LFP-E</b>
	Activated carbon filter cartridge	–	<b>532911</b>	<b>MS6-LFX</b>
High flow rate HF				
MS6	Micro-filter cartridge	0.01	<b>552093</b>	<b>MS6-LFM-A-HF</b>
	Fine-filter cartridge	1	<b>552092</b>	<b>MS6-LFM-B-HF</b>
	Activated carbon filter cartridge	–	<b>552094</b>	<b>MS6-LFX-HF</b>
Range of application HP, suitable for sealing air and cleaning air				
MS6	Micro-filter cartridge	0.01	<b>547922</b>	<b>MS6-LFM-AI</b> 
	Fine-filter cartridge	1	<b>547923</b>	<b>MS6-LFM-BI</b> 
	Activated carbon filter cartridge	–	<b>547925</b>	<b>MS6-LFX-AKI</b> 

## Filter cartridges

Accessories

### Filter cartridges, MS9 series




Ordering data				
Size	Filter cartridge	Grade of filtration [µm]	Part No.	Type
MS9	Micro-filter cartridge	0.01	553036	MS9-LFM-A
	Fine-filter cartridge	1	553037	MS9-LFM-B
	Filter cartridge	5	570309	MS9-LFP-C
	Filter cartridge	40	570310	MS9-LFP-E
	Activated carbon filter cartridge	–	552946	MS9-LFX
High flow rate HF				
MS9	Micro-filter cartridge	0.01	552944	MS9-LFM-A-HF
	Fine-filter cartridge	1	552945	MS9-LFM-B-HF

# Filter cartridges

Accessories

**FESTO**

Filter cartridges, MS12 series



Ordering data				
Size	Filter cartridge	Grade of filtration [µm]	Part No.	Type
MS12	Micro-filter cartridge	0.01	537146	MS12-LFM-A
	Fine-filter cartridge	1	537145	MS12-LFM-B
	Filter cartridge	5	537143	MS12-LFP-C
	Filter cartridge	40	537144	MS12-LFP-E
	Activated carbon filter cartridge	-	537147	MS12-LFX

- 2 - Type to be discontinued  
Available up to December 2014


FESTO

## Filter cartridges

Accessories

### Filter cartridges, H series

- For fine and micro filters, H series
- For adsorption dryer LDF



Ordering data							
Filter cartridge	Grade of filtration [µm]	For adsorption dryer LDF	Connection	D1 ∅	D2 ∅	L1	Part No. Type
Micro-filter cartridge	0.01	Inlet filter (LDF-H1-...-H3)	G1/4	35	6.75	74	<b>185688</b> LFMAP-1/4-H
		Inlet filter (LDF-H4-...-H7)	G1/2	48	21.7	126	<b>162824</b> LFMAP-1/2-H
		-	G3/4	72	33	168.8	<b>162825</b> LFMAP-3/4-H
		-	G1	72	33	268.8	<b>162826</b> LFMAP-1-H
Fine-filter cartridge	1	Outlet filter (LDF-H1-...-H3)	G1/4	35	6.75	74	<b>185689</b> LFMBP-1/4-H
		Outlet filter (LDF-H4-...-H7)	G1/2	48	21.7	126	<b>162827</b> LFMBP-1/2-H
		-	G3/4	72	33	168.8	<b>162828</b> LFMBP-3/4-H
		-	G1	72	33	268.8	<b>162829</b> LFMBP-1-H