## Type codes

001	Series	
KRP	Connecting cable, socket connection pattern ZC, self-tapping screw	
002	Variant	
1	Variant 1	

003	Rated operating voltage	
24	24 V DC	
004	Cable length [m]	
2.5	2.5	
5	5	

## Connecting cables, socket, plug pattern ZC, self-tapping screw

### Datasheet

#### Connecting cable KRP-1

- Connecting cable for connecting relay plates (valve terminal CPV10 and CPV14)
- Pre-assembled
- Cable lengths: 2.5 m and 5 m
- 2-pin socket
- Not suitable for energy chains



#### General technical data

Type of mounting	Via through-hole
Mounting position	Any

#### Technical data - Electrical connection

Electrical connection	2-pin, angled socket

#### Technical data - Electrics

Operating voltage range DC	≤26 V
Operating voltage range AC	≤20 V
Current rating	1A

#### Technical data - Cable

Cable diameter	3.5 mm
Cable composition	2 x 0.25 mm <sup>2</sup>

#### Materials

Housing material	PUR
Cable sheath material	PVC
Pin contacts material	Bronze
LABS (PWIS) conformity	VDMA24364-B2-L

#### Operating and environmental conditions


Ambient temperature	-10 50 °C
CE marking (see declaration of conformity) <sup>1)</sup>	To EU RoHS Directive
UKCA marking (see declaration of conformity) <sup>2)</sup>	To UK RoHS regulations
Degree of protection	IP65

<sup>1)</sup> Additional information: www.festo.com/catalogue/pun-h  $\longrightarrow$  Support/Downloads.

<sup>2)</sup> Additional information: www.festo.com/catalogue/pun-h  $\longrightarrow$  Support/Downloads.

## Datasheet

# Dimensions



- [2] Holder for inscription label (IBS-6x10)
- [3] 2-core cable 2.5 m or 5 m (2x0.25 mm<sup>2</sup>)
- [5] Retaining screw

Download CAD data  $\rightarrow \underline{\text{www.festo.com}}$ 

Туре	B1	D1	H1	H2	L1	L2
		Ø				
KRP-1	9.8	3.4	16.4	12	28.3	18

Ordering data							
Electrical connection		Cable length	Weight	Part no.	Туре		
Field device side	Controller side	[m]	[g]				
Socket, plug pattern ZC, self-tapping screw	Open cable end	2.5	49	165612	KRP-1-24-2.5		
		5	94	165613	KRP-1-24-5		
	Field device side	Field device side Controller side	Field device side Controller side [m]	Field device side     Controller side     [m]     [g]       Socket, plug pattern ZC, self-tapping screw     Open cable end     2.5     49	Field device side Controller side [m] [g]  Socket, plug pattern ZC, self-tapping screw Open cable end 2.5 49 165612		

Orderin	Ordering data – Accessories						
				Part no.	Туре		
		Inscription labels in frames, pack of 64	6x10 mm	18576	IBS-6x10		