

## Quick Star Push-in Connectors – Inch Series



QSM – Mini Series:  
Tubing O.D. from 1/8" to 3/16"

QS – Standard Series:  
Tubing O.D. from 1/8" to 5/8"

For complete dimensional and technical information, visit: [www.festo.com/us](http://www.festo.com/us) and view our online catalog, or contact your Product Support team via:  
Phone: 1.800.99.FESTO (1.800.993.3786)  
Email: [product.support@us.festo.com](mailto:product.support@us.festo.com)

## Push-in Straight Connector



Ordering Data		
Part No.	Type	For Tubing O.D. D1 [inch]
153905*	QSM-1/8T-U	1/8
195588*	QSM-5/32T-U	5/32
153628*	QS-5/32T-U	5/32
153629*	QS-3/16T-U	3/16
153630*	QS-1/4T-U	1/4
153631*	QS-5/16T-U	5/16
153632*	QS-3/8T-U	3/8
153633	QS-1/2T-U	1/2
190589*	QS-5/8T-U	5/8

2

2.1

## Push-in Reducing Straight Connector



Ordering Data			
Part No.	Type	For Tubing O.D. D1 [inch]	For Tubing O.D. D2 [inch]
153906*	QSM-5/32T-1/8-U	5/32	1/8
153634*	QS-3/16T-5/32-U	3/16	5/32
190590*	QS-1/4T-5/32-U	1/4	5/32
153635*	QS-1/4T-3/16-U	1/4	3/16
153636*	QS-5/16T-1/4-U	5/16	1/4
153637*	QS-3/8T-5/16-U	3/8	5/16
153638	QS-1/2T-3/8-U	1/2	3/8
190591*	QS-5/8T-1/2-U	5/8	1/2

## Push-in Straight Connector, with Internal Shut-off



Ordering Data		
Part No.	Type	For Tubing O.D. D1 [inch]
190592	QSMK-1/8T-U	1/8
190593	QSMK-5/32T-U	5/32
190594	QSMK-3/16T-U	3/16
190595	QSK-1/4T-U	1/4
190596	QSK-5/16T-U	5/16
190597	QSK-3/8T-U	3/8
190598	QSK-1/2T-U	1/2

\* Packaged in quantities of 10. (No asterisk = items sold by the unit.)  
Ask Festo or your authorized Festo distributor about part numbers of items offered in bulk package sizes.

**Push-in Reducing Straight Connector with Insert**



Ordering Data			
Part No.	Type	For Tubing O.D. D1 [inch]	For Tubing O.D. D2 [inch]
190613*	QSM-5/32H-1/8-U	5/32	1/8
190614*	QSM-3/16H-5/32-U	3/16	5/32
190615*	QS-1/4H-3/16-U	1/4	3/16
190616*	QS-5/16H-1/4-U	5/16	1/4
190617*	QS-3/8H-5/16-U	3/8	5/16
190618*	QS-1/2H-3/8-U	1/2	3/8

**Push-in Elbow Connector**



Ordering Data		
Part No.	Type	For Tubing O.D. D1 [inch]
153913*	QSML-1/8T-U	1/8
190602*	QSML-5/32T-U	5/32
153662*	QSL-5/32T-U	5/32
153663*	QSL-3/16T-U	3/16
153664*	QSL-1/4T-U	1/4
153665*	QSL-5/16T-U	5/16
153666*	QSL-3/8T-U	3/8
153667	QSL-1/2T-U	1/2
190603*	QSL-5/8T-U	5/8

**Push-in Elbow Connector, with Insert**



Ordering Data		
Part No.	Type	For Tubing O.D. D1 [inch]
190620*	QSML-1/8H-U	1/8
190621*	QSML-5/32H-U	5/32
190622*	QSML-3/16H-U	3/16
153654*	QSL-1/4H-U	1/4
153655*	QSL-5/16H-U	5/16
153656*	QSL-3/8H-U	3/8
190623*	QSL-1/2H-U	1/2

\* Packaged in quantities of 10. (No asterisk = items sold by the unit.)  
Ask Festo or your authorized Festo distributor about part numbers of items offered in bulk package sizes.

**Push-in Elbow Connector, with Long Insert**



Ordering Data		
Part No.	Type	For Tubing O.D. D1 [inch]
190636*	QSML-3/16HL-U	3/16
190635*	QSL-5/32HL-U	5/32
153659*	QSL-1/4HL-U	1/4
153660*	QSL-5/16HL-U	5/16
153661*	QSL-3/8HL-U	3/8
190637*	QSL-1/2HL-U	1/2

**Push-in Reducing Elbow Connector, with Insert**



Ordering Data			
Part No.	Type	For Tubing O.D. D1 [inch]	For Tubing O.D. D2 [inch]
190625*	QSML-5/32H-1/8-U	5/32	1/8
190626*	QSML-3/16H-1/8-U	3/16	1/8
190627*	QSML-3/16H-5/32-U	3/16	5/32
190628*	QSL-1/4H-5/32-U	1/4	5/32
190629*	QSL-1/4H-3/16-U	1/4	3/16
190630*	QSL-5/16H-3/16-U	5/16	3/16
153657*	QSL-5/16H-1/4-U	5/16	1/4
190631*	QSL-3/8H-1/4-U	3/8	1/4
153658*	QSL-3/8H-5/16-U	3/8	5/16
190632*	QSL-1/2H-5/16-U	1/2	5/16
190633*	QSL-1/2H-3/8-U	1/2	3/8

**Push-in Y Connector**



Ordering Data		
Part No.	Type	For Tubing O.D. D1 [inch]
153921*	QSMY-1/8T-U	1/8
190608*	QSMY-5/32T-U	5/32
153750*	QSY-5/32T-U	5/32
153751*	QSY-3/16T-U	3/16
153752*	QSY-1/4T-U	1/4
153753*	QSY-5/16T-U	5/16
153754*	QSY-3/8T-U	3/8
153755	QSY-1/2T-U	1/2

\* Packaged in quantities of 10. (No asterisk = items sold by the unit.)  
Ask Festo or your authorized Festo distributor about part numbers of items offered in bulk package sizes.

## Push-in Reducing Y Connector



Ordering Data			
Part No.	Type	For Tubing O.D. D1 [inch]	For Tubing O.D. D2 [inch]
153922*	QSMY-5/32T-1/8-U	5/32	1/8
153756*	QSY-3/16T-5/32-U	3/16	5/32
153757*	QSY-1/4T-3/16-U	1/4	3/16
153758*	QSY-5/16T-1/4-U	5/16	1/4
153759*	QSY-3/8T-5/16-U	3/8	5/16
153760	QSY-1/2T-3/8-U	1/2	3/8

## Push-in Reducing Double Y Connector



Ordering Data			
Part No.	Type	For Tubing O.D. D1 [inch]	For Tubing O.D. D2 [inch]
153814*	QSQ-3/16T-5/32-U	3/16	5/32
153815*	QSQ-1/4T-5/32-U	1/4	5/32
190609*	QSQ-1/4T-3/16-U	1/4	3/16
153816	QSQ-5/16T-1/4-U	5/16	1/4

## Push-in T Connector



Ordering Data		
Part No.	Type	For Tubing O.D. D1 [inch]
153920*	QSMT-1/8T-U	1/8
190604*	QSMT-5/32T-U	5/32
153724*	QST-5/32T-U	5/32
153725*	QST-3/16T-U	3/16
153726*	QST-1/4T-U	1/4
153727*	QST-5/16T-U	5/16
153728*	QST-3/8T-U	3/8
153729	QST-1/2T-U	1/2
190606*	QST-5/8T-U	5/8

\* Packaged in quantities of 10. (No asterisk = items sold by the unit.)  
 Ask Festo or your authorized Festo distributor about part numbers of items offered in bulk package sizes.

## Push-in Reducing T Connector



Ordering Data			
Part No.	Type	For Tubing O.D. D1 [inch]	For Tubing O.D. D2 [inch]
190605*	QSMT-5/32T-1/8-U	5/32	1/8
153730*	QST-3/16T-5/32-U	3/16	5/32
153731*	QST-1/4T-3/16-U	1/4	3/16
153732*	QST-5/16T-1/4-U	5/16	1/4
153733*	QST-3/8T-5/16-U	3/8	5/16
153734	QST-1/2T-3/8-U	1/2	3/8
190607*	QST-5/8T-1/2-U	5/8	1/2

## Push-in Triple Branch Reducing T Connector



Ordering Data			
Part No.	Type	For Tubing O.D. D1 [inch]	For Tubing O.D. D2 [inch]
153804	QST3-3/16T-5/32-U	3/16	5/32
153805	QST3-5/16T-5/32-U	5/16	5/32
153806	QST3-5/16T-3/16-U	5/16	3/16
153807	QST3-5/16T-1/4-U	5/16	1/4
153808	QST3-3/8T-1/4-U	3/8	1/4
153809	QST3-3/8T-5/16-U	3/8	5/16

## Push-in X Connector



Ordering Data		
Part No.	Type	For Tubing O.D. D1 [inch]
153923*	QSMX-1/8T-U	1/8
190610*	QSMX-5/32T-U	5/32
190611*	QSX-3/16T-U	3/16
190612*	QSX-1/4T-U	1/4
153840*	QSX-5/16T-U	5/16
153841*	QSX-3/8T-U	3/8
153842*	QSX-1/2T-U	1/2

\* Packaged in quantities of 10. (No asterisk = items sold by the unit.)  
 Ask Festo or your authorized Festo distributor about part numbers of items offered in bulk package sizes.

## Push-in Bulkhead Connector



Ordering Data		
Part No.	Type	For Tubing O.D. D1 [inch]
190599*	QSMS-1/8T-U	1/8
190600*	QSMS-5/32T-U	5/32
153761*	QSS-5/32T-U	5/32
153762*	QSS-3/16T-U	3/16
153763*	QSS-1/4T-U	1/4
153764*	QSS-5/16T-U	5/16
153765*	QSS-3/8T-U	3/8
153766*	QSS-1/2T-U	1/2
190601*	QSS-5/8T-U	5/8

## Push-in Cap



Ordering Data		
Part No.	Type	For Tubing O.D. D1 [inch]
153925*	QSC-1/8-U	1/8
153828*	QSC-5/32-U	5/32
153829*	QSC-3/16-U	3/16
153830*	QSC-1/4-U	1/4
153831*	QSC-5/16-U	5/16
153832*	QSC-3/8-U	3/8
153833*	QSC-1/2-U	1/2

## Blanking Plug



Ordering Data		
Part No.	Type	Plug Diameter D1 [inch]
153924*	QSMC-1/8H-U	1/8
153834*	QSC-5/32H-U	5/32
153835*	QSC-3/16H-U	3/16
153836*	QSC-1/2H-U	1/2
153837*	QSC-5/16H-U	5/16
153838*	QSC-3/8H-U	3/8
153839*	QSC-1/2H-U	1/2
190640*	QSC-5/8H-U	5/8

\* Packaged in quantities of 10. (No asterisk = items sold by the unit.)  
Ask Festo or your authorized Festo distributor about part numbers of items offered in bulk package sizes.

## Push-in Insert



Ordering Data		
Part No.	Type	Insert Diameter D1 [inch]
153817*	QSH-5/32-U	5/32
153818*	QSH-3/16-U	3/16
153819*	QSH-1/4-U	1/4
153820*	QSH-5/16-U	5/16
153821*	QSH-3/8-U	3/8
153822	QSH-1/2-U	1/2
190641*	QSH-5/8-U	5/8

2

## Push-in Reducing Insert



Ordering Data			
Part No.	Type	Insert Diameter D1 [inch]	Insert Diameter D2 [inch]
153823*	QSH-3/16-5/32-U	3/16	5/32
153824*	QSH-1/4-3/16-U	1/4	3/16
153825*	QSH-5/16-1/4-U	5/16	1/4
153826*	QSH-3/8-5/16-U	3/8	5/16
153827*	QSH-1/2-3/8-U	1/2	3/8
190642*	QSH-5/8-1/2-U	5/8	1/2

\* Packaged in quantities of 10. (No asterisk = items sold by the unit.)  
 Ask Festo or your authorized Festo distributor about part numbers of items offered in bulk package sizes.